






ROHS



PCB Layout Diagram
Top View



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

1.MATERIAL:

- a.HOUSING:LCP UL94V-0
b.CONTACT:PHOSPHOR BRONZE
(SURFACE PLATING:Sn100u"-120u")

2.ELECTRIC:

- a.CONTACT RESISTANCE: 50 MILLIOHMS MAX
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
d.OPERATING TEMPERATURE: -25°C~ +85°C

3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.15mm	Sn Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.15mm	Sn Plating
1	HOUSING	1	LCP	WHITE
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
COSTOMTER DRAWING		深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
DRAWING		TITLE 电池座适用电池规格CR2032 REV. A		
CHECK				
APPROVAL				
TOLERANCES ARE		PART NO. LAIL-CR2032-SMT-B06-4AK DWG.NO.	UNITS mm Projection	
30-150	±0.35			
10-30	±0.2			
5-10	±0.15			
0-5	±0.1			
ANGLE		±3°		