

RoHS



机壳面板

全周0.20

密封圈

前后组装方式

此处点胶

Note:

1.Material:

1.1 InsertMolding: LCP UL 94V-0 Black

1.2 Contact:C2680,t=0.20mm middleclip SUS t=0.15mm

1.3 Shell: Zinc Alloy.表面镀100U"

1.4 Waterproof ring:red silicone

2.ELECTRICAL:

2-1:CURUENT RATAING:

VBUS AND GND CONTACTS RATED AT 5A

PARALLELED FOR A TOTAL OF 5A;

2-2:INITIAL CONTACT RESISTANCE :40 MILLIOHMS MAX

2-3:DIEELECTRIC WITHSTANDING VOLTAGE:

100V AC ;

3:MECHANICAL CHARACTERISTICS:

3-1:MATING FORCE:5~20N

3-2:UNMATING FORCE:8~20N(INITIAL),

6~20N(AFTER 10000 CYCLES)

3-3:FREQUENCE: 200±50 CYCLES /HOUR,10000 CYCLES

3-4:OPERATING TEMPERATURE ;-40°~80°.

4: WATERPROOF: IP-X7.

PIN ASSIGNMENTS

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.35	X'.	±5°
.X	±0.30	.X"	±2°
.XX	±0.25	.XX"	±1°
.XXY	±0.10	.XXY"	±0.5°



深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位
UNITS

MM

制图
DRAWING

Erick

产品料号
PRODUCT PART NO.

918-418K2028S40005

比例
SCALE

1:1

审核
CHKD

L S S

产品名称
PRODUCT NO.

TYPE-C 6pin 沉板1.6压铸防水

日期
DATE

2021/03/10

核准
APPD

黄国荣

角法
VIEW

版本
VER

A0

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm