





PIN	Ø 1.65	Ø 2.0	Ø 2.5
APPO			

REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK

P.C.B LAYOUT




Material declaration		
No.	NAME	Description
① A	基座	PPA 热塑性塑胶[黑色]
② B	内芯针	H62 黄铜 Ø2.5[镀银]
③ C	静态端子	黄铜 H62[镀银/锡基 50u" min]
④ D	动态端子	磷铜 H65[镀银/锡基 50u" min]
⑤ E	外壳	黄铜 H62[镀银/锡基 50u" min]

DC-022D - TXX

产品型号
材质/内芯
T20=全铜内芯2.0mm
T25=全铜内芯2.5mm

CIRCUIT DIAGRAM



LEVEL		A[better product]	B[average product]
PROJECT	Contact Rating	2A, 24V DC	
	Initial Contact Resistance	50mΩ max.	
Properties	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
	Withstand Voltage	500V AC for 1 minute	350 V AC for 1 minut
Durable Performance	There No Load	6,000 Cycles	5,000 Cycles
	Rated Load	5,000 Cycles	4,000 Cycles
Storage temp.		-35℃~+75℃(Operating Temp:)	
Operating Force		IF:35N MAX. (EF:10.ON MIN.)	
Heat Rrsistance		IR Reflow:235℃,5sec. Manual:350℃,3sec.	

DIMENSION CLASSIFICATION	
■	CRITICAL
☒	MAJOR

TOLERANCE TABLE

.X	±	0.40
.XX	±	0.25
.XXX	±	0.10
ANGLE	±	2°

台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD		TITLE DC-022D 立插/焊线式 带螺孔5.5DC电源插座		開關,連接器 SOFNG	
PART NO.	DC-022D	SERIES	SD106		
APPROVED	Peck	DWG NO.	SOF-G006		
CHECKED	Paul	SCALE	1:1	UNIT	mm
DRAWIN	David	REV	AO	SHEET NO.	1/1