






ROHS



PCB Layout Diagram
Top View

1.MATERIAL:

- a.HOUSING:PPA
b.CONTACT:PHOSPHOR BRONZE
(SURFACE PLATING: Au1u")

SEE ORDERING INFORMATION

2.ELECTRIC:

- a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
c.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE
d.OPERATING TEMPERATURE: -25°C~ +85°C

3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20	Gold Plating and Ni Under-Plating			
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20	Gold Plating and Ni Under-Plating			
1	HOUSING	1	PPA	BROWN			
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR			
COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE	电池底座适用电池规格CR1220	REV.	A	
30-150	±0.35	ANGLE	PART NO.	LAIL-CR1220-SMT-B03-2AA	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			±3°	DWG.NO.		Projection	