

Operation:DIP&电源连接器



ITEM NO.:DC-025M-X25 (Series)
(L14.7×W10.8 DC-POWER-SOCKETS)



Technical parameter

PROJECT	LEVEL	LEVEL	
		A[better product]	B[average product]
Electrical Properties	Contact Rating	3.0A, 24V DC	
	Initial Contact Resistance	50mΩ max.	100mΩ max.
	Insulation Resistance	100MΩ min.500V DC	Skey/PD: 100MΩ min.300V DC
	Withstand Voltage	500V AC for 1 minute	350 V AC for 1 minut
	There No Load	6,000 Cycles	5,000 Cycles
Durable Performance	Rated Load	5,000 Cycles	4,000 Cycles
	Storage temp.	-35℃~+75℃(Operating Temp:)	

直立插装 DIP

正向導入 LATERAL




精密部品 NICETY

可靠 STABILIZE

適合環保 RoHS

Unit:mm

PIN=2.0/2.5mm



DC - 025M - X25

产品型号
内芯直径

Operating Force

Inward

5.0~8.0N. (1N.=100gram-force)

Exiting

5.0~8.0N. (1N.=100gram-force)


Solder-ability (Max.)

IR Reflow:245°C, 5sec.

Manual:330°C, 3sec.



邀您使用(微信)小程序
碩方电子开关&连接器选型手册
手机扫码即可进入...



Pin Definition





Material declaration

No.	NAME	Type	Description
① A	FLAT PIECE	1	H62 黄铜 BRASS[镀银]
② B	CURVE PIECE	1	H62 黄铜 BRASS[镀银]
③ C	SPRING	1	磷青铜 BRONZE
④ D	PIN	1	H59 BRASS
⑤ E	AXIS SUPPORT	1	H62 黄铜 BRASS[镀银]
⑥ F	HOUSING	1	耐热尼龙 PA66

PIN	φ 1.3	φ 2.0	φ 2.5
APPO			

CIRCUIT DIAGRAM



本品不屬於危害性廢棄物,須丟棄時可以委託
回收商予以回收再生處理。
Products do not belong to •

注記 NOTICE

- 碩方公司擁有最終解釋權; The company reserves the right of final interpretation;
- 文件禁止外洩、轉載; Leaked and reproduced prohibited;
- 未經授權修改無效。Modify is invalid.

運送時本產品不要直接與水、酸鹼性化學物質
接觸,或放置於含有以上氣體環境中,並且需要
注意會有滑落、側翻的危險發生; 運輸過程中
不能有碰撞或者擠壓,須保證溫度與濕度適中
[常溫 25°C,濕度在 50°C 以內],不可導致材料變
形或氧化。