





LEVEL		A[better product]		B[average product]	
PROJECT					
Electrical Properties	Contact Rating	2A, 24V DC			
	Initial Contact Resistance	50mΩ max.			
	Insulation Resistance	100MΩ min.500V DC		Skey/PD: 100MΩ min.300V DC	
	Withstand Voltage	500V AC for 1 minute		350 V AC for 1 minut	
Durable Performance	There No Load	6,000 Cycles		5,000 Cycles	
	Rated Load	5,000 Cycles		4,000 Cycles	
Storage temp.		-35℃～+75℃(Operating Temp:)			
Operating Force		IF:35N MAX. (EF:10.ON MIN.)			
Heat Rrsistance		IR Reflow:235℃, 5sec. Manual:350℃, 3sec.			


REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK

Material declaration		
No.	NAME	Description
① A	基座	PPA 热塑性塑胶[黑色]
② B	内芯针	H62 黄铜 Φ2/2.5[镀银]
③ C	静态端子	黄铜 H62[镀银/锡基 50u" min]
④ D	动态端子	磷铜 H65[镀银/锡基 50u" min]
⑤ E	外壳	黄铜 H62[镀银/锡基 50u" min]

邀您使用(微信)小程序
硕方电子开关&连接器选型手册
手机扫码即可进入...



DIMENSION CLASSIFICATION ■ : CRITICAL ☒ : MAJOR		台湾硕方精密电子科技有限公司 TAIWAN SOFENG PRECISION ELECTRONIC CO., LTD		SOFENG	
TOLERANCE TABLE		TITLE	DC-022B 立插/焊线式 5.5DC电源插座	開關,連接器	
.X	± 0.40	PART NO.	DC-022B	SERIES	SD106
.XX	± 0.25	APPROVED	Peck	DWG NO.	SOF-G006
.XXX	± 0.10	CHECKED	Paul	SCALE 1:1	UNIT mm SIZE A4
ANGLE	± 2°	DRAWIN	David	REV	AO SHEET NO. 1/1



DC-022B - TXX

产品型号

材质/内芯
T20=全铜内芯2.0mm
T25=全铜内芯2.5mm