




1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.03	阿树




SCHEMATIC


SPECIFICATION

Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min.500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.25mm
Operating Temp: -30℃~+85℃
Storage Temp: -30℃~+80℃

PAPT NO	TS-1102T-B
Operating Force	A:100gf B:160gf C:260gf
Height	D:7.3



Recommended P.C.B layout




AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

阿树



UNIT: mm/in

SIZE: A4

MODEL TYPE:
TACT SWITCHPART NO.:
TS-1102T-BDWG NO.:
TS-1102T-B

SCALE	PAGE	REVISION
N/A	1/1	A1

1

2

3

4