








Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:2A AC/DC
额定电流: 2A AC/DC
Withstanding voltage:1200V AC/minute
耐受电压: 1200V AC/分钟
Temperature range:-40℃~+125℃
温度范围: -40℃~+125℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:10mΩ Max
接触电阻: 10mΩ Max



X25072 H I - 04 F 00 - PT SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
- 2.Category:H-HSG
- 3.Category:I-Punctured type
- 4.Row No.Pin No:XX-02~17 Pin
- 5.Appearance type:F Type
- 6.Spacer bar:For example12-Keying between pin 1 and pin 2
23-Keying between pin 2 and pin 3...When the pin number is above 10,use the letters A,B C...A for 10,B for 11...
Blank-No Keying
- 7.Material:PT-PBT ;N0-PA66 UL 94V-0
- 8.Plating:SN-Plated Tin ; V01-Gold Flash;V03-Gold 3u;
V15-Gold 15u;V30-Gold 30u



Poles	Dimensions(mm)		Spacer bar	C	D
	A	B			
02	7.40	2.50	00	/	/
03	9.90	5.00	12	7.40	2.50
04	12.40	7.50	23	9.90	5.00
05	14.90	10.00	34	12.40	7.50
06	17.40	12.50	45	14.90	10.00
07	19.90	15.00	56	17.40	12.50
08	22.40	17.50	67	19.90	15.00
09	24.90	20.00	78	22.40	17.50
10	27.40	22.50	89	24.90	20.00
11	29.90	25.00	9A	27.40	22.50
12	32.40	27.50	AB	29.90	25.00
13	34.90	30.00	BC	32.40	27.50
14	37.40	32.50	CD	34.90	30.00
15	39.90	35.00	DE	37.40	32.50
16	42.40	37.50	EF	39.90	35.00
17	44.90	40.00	FG	42.40	37.50
			GH	44.90	40.00

X25072HI-04F00-PTSN	AWG24~22	Phosphor	X25072W
PART NO	Wire Range	Material(Pin)	Suitable XKB Wafer

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.5mm Pitch Rast Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X25072HI-04F00-PTSN
		DWG NO.:
		X-X25072HI-04F00-PTSN

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5

REVISIONS					UNSPECIFIED TOLERANCES	
	DESCRIPTION	DATE	REVISED	APPROVED		

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0