






ROHS



PCB Layout Diagram  
Top View

NOTE:

1.MATERIAL:

a.HOUSING:PPA

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING: Au1U")

SEE ORDERING INFORMATION


2.ELECTRIC:

a.CONTACT RESISTANCE: 30 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

d.OPERATING TEMPERATURE: -25°C~ +85°C



|                  |             |                                                             |                         |                                                                                                  |       |    |
|------------------|-------------|-------------------------------------------------------------|-------------------------|--------------------------------------------------------------------------------------------------|-------|----|
| 3                | TERMINAL(-) | 1                                                           | PHOSPHOR BRONZE, T=0.20 | Gold Plating and Ni Under-Plating                                                                |       |    |
| 2                | TERMINAL(+) | 1                                                           | PHOSPHOR BRONZE, T=0.25 | Gold Plating and Ni Under-Plating                                                                |       |    |
| 1                | HOUSING     | 1                                                           | PPA                     | BROWN                                                                                            |       |    |
| NO.              | PART NAME   | Q'TY                                                        | MATERIAL                | PLATING & COLOR                                                                                  |       |    |
| COSTOMER DRAWING |             | LAILIAN 深圳市莱联电子有限公司<br>SHENZHEN LAILIAN ELECTRONICS CO.,LTD |                         |                                                                                                  |       |    |
| DRAWING          |             |                                                             |                         |                                                                                                  |       |    |
| CHECK            |             |                                                             |                         |                                                                                                  |       |    |
| APPROVAL         |             |                                                             |                         |                                                                                                  |       |    |
| TOLERANCES ARE   |             | TITLE                                                       | 电池座适用电池规格CR2032         | REV.                                                                                             | A     |    |
| 30-150           | ±0.35       | ANGLE                                                       | PART NO.                | LAIL-CR2032-DIP90-B05-1BJ                                                                        | UNITS | mm |
| 10-30            | ±0.2        |                                                             |                         |                                                                                                  |       |    |
| 5-10             | ±0.15       |                                                             |                         |                                                                                                  |       |    |
| 0-5              | ±0.1        |                                                             |                         |                                                                                                  |       |    |
|                  |             | ±3°                                                         | DWG.NO.                 | Projection  |       |    |