








REV NO.	DATE	REVISION	DR	CH	APP
△					

SPECIFICATION

1. Rating : DC12V 0.5A~24V 0.3A.
2. Contact Resistance : 30mΩ Max.
3. Travel : 1.6mm.
4. Operating Force : 250 ± 150gf.
5. Life Cycle : 2,000 Cycle (with load).
6. Packing : 200pcs Vinyl Bag
7. Body Color : Orange



						DRAW/DESIGNED	CHECKED	APPROVED		G.TOL	TITLE	MINI SLIDE SWITCH	
						K.N KIM	K.N KIM	W.J LEE		--			
						2026-07-03	2026-07-03	2026-07-03	UNIT	SCALE	MODEL NO.	SSIL-10-ORK	REV.
									mm	N:S			
										SIZE	DRAW NO.	SSIL-10-ORK-01	01
										A4			

Din ISO-2768-1m					
Ranges	0.5~3	3~6	6~30	30~120	120~400
Tolerance	±0.1	±0.1	±0.2	±0.3	±0.5

SUNGMUN ELECTRONICS CO.,LTD