

RoHS

REV.

ECN.#

DESCRIPTION

NAME






DATE

A0

NEW RELEASE

HZP

2023.01.02



Recommended PCB Layout
(Tolerance: ± 0.05)

1. Material:

1.1 Housing: PBT UL94V-0 Black.

Insert: PBT UL94V-0 Black.

1.2 Shell: SUS 201.

1.3 RJ45 Terminal: Phosphor Bronze (C5191) T=0.35mm
Plating: 50u" Gold Plated On Contact Area,
80u" ~120u" Tin Plated On Solder Area,
50u" ~80u" Ni Underplated Overall.

1.4 Tail Terminal: Brass (C2680) T=0.35mm,
Plating: 80u" ~120u" Tin Plated Over,
30u" ~50u" Ni Underplated Overall.

2. Environmental requirements:

2.1 Lead-free process, compliant RoHS.

MILLIMETERS	INCH
X.* $\pm 2^*$	X.* $\pm 2^*$
.X ± 0.30	.X ± 0.012
.XX ± 0.20	.XX ± 0.008
.XXX ± 0.10	.XXX ± 0.004





THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF DongGuan JinBiLai
Metal Plastic Technology Co., Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE
PRIOR WRITTEN CONSENT OF DongGuan
JinBiLai Metal Plastic Technology Co., Ltd



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	RJ45 正向板上DIP L21.10 无灯带弹 空包	DR		
PART NO.	109435691-A	CHKD		
PRO J.	PAGE 2/2 UNITS mm	APPD		
SIZE	A4 SCALE 1:1 DIS NO.			

RoHS



作 业 说 明

1. 根据物料清单备好所需包材；
2. 接上工序所传已做好之产品以水平放置统一方向放入吸塑盒内。 如图所示, 每盘吸塑盒内放120PCS；
3. 将放满产品的吸塑盒底用盒盖叠放吻合, 一箱装10盘
4. 外箱用胶布工字型封箱, 并在外箱贴上相应标签

注 意 事 项

1. 吸塑盒内产品不可多装, 少装, 方向须做到一致；
2. 有未装满之纸箱须使用泡棉或其它不影响品质之物品填充且在纸箱麦头或标签上注明尾数；
3. 确认所使用包材无钉或铁扣之类连接；

120	10	1200PCS	--KG	--KG
PCS/ TRAY	TRAY/ CARTON	QUANTITY	GROSS WEIGHT	NET WEIGHT

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD							
X' ±2'	X' ±2'	X' ±2'	X' ±2'								
X ±0.30	X ±0.012	TITLE				RJ45 正向板上DIP L21.10 无灯带弹 空包		DR			
XX ±0.20	XX ±0.008										
XXX ±0.10	XXX ±0.004										
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd				PART NO.		109435691-A		CHKD			
				PRO J.		PAGE	2/2	UNITS	mm	APPD	
						SIZE	A4	SCALE	1:1	DIS NO.	