






RoHS

REV.	ECN.#	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	liuhongping	2023.01.02
A1		修改结构，以配合自动机生产， 包装数量改小，以改善运输过程中端子脚变形问题。	liuhongping	2025.10.27
A2		修改结构，以配合自动机生产，	liuhongping	2025.11.28

NOTES:

- MATERIAL:
 - HOUSING: PA46 UL94V-0; COLOR: BLACK
 - COVER: PA46 UL94V-0; COLOR: BLACK
 - TERMINAL: C51000
 - SHELL: C2680
- FINISH:
 - TERMINAL: G/F PLATED ON CONTACT AREA;
G/F PLATED ON SOLDER AREA;
Ni 20u" MIN. UNDERPLATED OVERALL.
 - SHELL: Ni 20u" MIN. PLATED OVERALL
 - LED: Tin 50u" MIN. PLATED OVERALL.
- ELECTRICAL SPECIFICATION:
 - LOAD RATING: 125VAC,1.5A;
 - CONTACT RESISTANCE: 40mΩ MAX(INITIAL). 50mΩ MAX (AFTER).
 - INSULATION RESISTANCE: 500MΩ MIN.
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC.
- MACHINERY SPECIFICATION:
 - MATING FORCE: 22.4N MAX.
UNMATING FORCE: 22.4N MAX.
 - DURABILITY: 750 CYCLES MIN.
- ENVIRONMENTAL SPECIFICATION:
 - OPERATING CONDITION: TEMPERATURE-40°C~+85°C;
HUMIDITY 80% R.H MAX
 - SALT SPRAY: 24H (CONTACT)
- SOLDER ABILITY: 245±5°C, 5±0.5s
- WAVE SOLDERING: SOLDER TEMPERATURE 235°C~260°C



Yellow LED		Green LED	
A9	—>	A10	—>
B9	—>	B10	—>
A11	—>	A12	—>
B11	—>	B12	—>





MILLIMETERS	INCH
X* ±2*	X* ±2*
X ±0.30	.X ±0.012
XX ±0.20	.XX ±0.008
XXX ±0.10	.XXX ±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	RJ45 2x2 8P8C 3侧正弹片 板上DIP 有柱 H27.25 黄绿LED	DR	
PART NO.	109315161	CHKD	
PRO J.	PAGE 1/2 UNITS mm	APPD	
SIZE	A4 SCALE 1:1 DIS NO.		

RoHS



作业说明

1. 根据物料清单备好所需包材；
2. 接上工序所传已做好之产品以水平放置统一方向放入吸塑盒内。 如图所示，每盘吸塑盒内放20PCS；
3. 将放满产品的吸塑盒底用盒盖叠放吻合，一箱装25盘
4. 外箱用胶布工字型封箱，并在外箱贴上相应标签

注意事项

1. 吸塑盒内产品不可多装，少装，方向须做到一致；
2. 有未装满之纸箱须使用泡棉或其它不影响品质之物品填充且在纸箱麦头或标签上注明尾数；
3. 确认所使用包材无钉或铁扣之类连接；

20	25	500PCS	--KG	--KG
PCS/ TRAY	TRAY/ CARTON	QUANTITY	GROSS WEIGHT	NET WEIGHT

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X" ±2"	X" ±2"	X" ±2"	X" ±2"				
X ±0.30	.X ±0.012	.X ±0.012	.X ±0.012	TITLE RJ45 2x2 8P8C 3侧正弹片 板上DIP 有柱 H27.25 黄绿LED			
XX ±0.20	.XX ±0.008	.XX ±0.008	.XX ±0.008	DR			
XXX ±0.10	.XXX ±0.004	.XXX ±0.004	.XXX ±0.004	PART NO. 109315161			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd				PRO J.		CHKD	
				PAGE	2/2	UNITS	mm
				SIZE	A4	SCALE	1:1
				DIS NO.			