






RoHS

REV.	ECN.#	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	liuhongping	2023.01.02



RECOMMENDED P.C.B LAYOUT
TOP VIEW (COMPONENT SIDE)

NOTES:

1. MATERIAL:

1.1 HOUSING: PBT ; COLOR: BLACK

1.2 TERMINAL: C51000

1.3 SHELL: C2680

2. FINISH:

2.1 TERMINAL: G/F PLATED ON CONTACT AREA;

G/F PLATED ON SOLDER AREA;

Ni 20u" MIN. UNDERPLATED OVERALL.

2.2 SHELL: Ni 20u" MIN. PLATED ON SOLDER AREA;

3. ELECTRICAL SPECIFICATION:

3.1 RATED CURRENT: 1.5A

3.3 CONTACT RESISTANCE: 40m Ω MAX(INITIAL). 50mΩ MAX (AFTER).

3.4 INSULATION RESISTANCE: 500MΩ MIN.

3.5 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC.

4. MACHINERY SPECIFICATION:

4.1 MATING FORCE: 22.4N MAX.

UNMATING FORCE: 22.4N MAX.

4.2 DURABILITY: 750 CYCLES MIN.

5. ENVIRONMENTAL SPECIFICATION :

5.1 OPERATING CONDITION: TEMPERATURE-40°C~+60°C; HUMIDITY 80% R.H MAX

5.2 SALT SPRAY: 8H

6. SOLDER ABILITY: 245±5°C, 5±0.5s

7. WAVE SOLDERING: SOLDER TEMPERATURE 235 ~ 260℃





MILLIMETERS	INCH
X.* ±2*	X.* ±2*
X ±0.30	.X ±0.012
XX ±0.20	.XX ±0.008
XXX ±0.10	.XXX ±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	RJ45 立式180度 H16.35 DIP包壳不带灯			DR		
PART NO.	109311401			CHKD		
PRO J.	PAGE	1/2	UNITS	mm	APPD	
SIZE	A4	SCALE	1:1	DIS NO.		

RoHS



400x285x345

作 业 说 明

1. 根据物料清单备好所需包材；
2. 接上工序所传已做好之产品以水平放置统一方向放入吸塑盒内。 如图所示, 每盘吸塑盒内放100PCS；
3. 将放满产品的吸塑盒底用盒盖叠放吻合, 一箱装 36盘
4. 外箱用胶布工字型封箱, 并在外箱贴上相应标签

注 意 事 项

1. 吸塑盒内产品不可多装, 少装, 方向须做到一致；
2. 有未装满之纸箱须使用泡棉或其它不影响品质之物品填充且在纸箱麦头或标签上注明尾数；
3. 确认所使用包材无钉或铁扣之类连接；

100	36	3600PCS	--KG	--KG
PCS/ TRAY	TRAY/ CARTON	QUANTITY	GROSS WEIGHT	NET WEIGHT

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X" ±2"	X" ±2"	X" ±2"	X" ±2"				
X ±0.30	.X ±0.012	.X ±0.012	.X ±0.012	TITLE		DR	
XX ±0.20	.XX ±0.008	.XX ±0.008	.XX ±0.008	PART NO.		CHKD	
XXX ±0.10	.XXX ±0.004	.XXX ±0.004	.XXX ±0.004	PRO J.		APPD	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd				SIZE	A4	SCALE	1:1
				DIS NO.			