





RoHS



REV.

ECN.#

DESCRIPTION

NAME

DATE

A0

NEW RELEASE

liuhongping

2023.01.02

NOTES:

1. MATERIAL:

1.1 HOUSING: PA46 UL94V-0; COLOR: BLACK

1.2 TERMINAL: C51000 Ø0.46mm

1.3 SHELL: SUS304

2. FINISH:

2.1 TERMINAL: G/F PLATED ON CONTACT AREA;

G/F PLATED ON SOLDER AREA;

Ni 30u" MIN. UNDERPLATED OVERALL.

2.2 SHELL: Ni 30u" MIN. PLATED OVERALL

2.3 LED: Tin 50u" MIN. PLATED OVERALL.

3. ELECTRICAL SPECIFICATION:

3.1 LOAD RATING: 125VAC, 1.5A;

3.3 CONTACT RESISTANCE: 40mΩ MAX (INITIAL). 50mΩ MAX (AFTER).

3.4 INSULATION RESISTANCE: 500MΩ MIN.

3.5 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC.

4. MACHINERY SPECIFICATION:

4.1 DURABILITY: 750 CYCLES MIN.

5. ENVIRONMENTAL SPECIFICATION:


5.1 OPERATING CONDITION: TEMPERATURE -40°C~+85°C;

HUMIDITY 80% R.H MAX

5.2 SALT SPRAY: 8H

6. SOLDER ABILITY: 245±5°C, 5±0.5s

7. WAVE SOLDERING: SOLDER TEMPERATURE 235°C~260°C



黄LED	9	10
绿LED	11	12




MILLIMETERS	INCH
X" ±2"	X" ±2"
X ±0.30	.X ±0.012
XX ±0.20	.XX ±0.008
XXX ±0.10	.XXX ±0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	RJ45 8P8C 屏蔽 板上DIP 有柱 H13.20 黄绿LED	DR	
PART NO.	109315141	CHKD	
PRO J.	PAGE 1/2 UNITS mm APPD		
SIZE	A4 SCALE 1:1 DIS NO.		

RoHS




作 业 说 明

1. 根据物料清单备好所需包材；
2. 接上工序所传已做好之产品以水平放置统一方向放入吸塑盒内。 如图所示, 每盘吸塑盒内放100PCS；
3. 将放满产品的吸塑盒底用盒盖叠放吻合, 一箱装50盘
4. 外箱用胶布工字型封箱, 并在外箱贴上相应标签

注 意 事 项

1. 吸塑盒内产品不可多装, 少装, 方向须做到一致；
2. 有未装满之纸箱须使用泡棉或其它不影响品质之物品填充且在纸箱麦头或标签上注明尾数；
3. 确认所使用包材无钉或铁扣之类连接；



100	50	5000PCS	--KG	--KG
PCS/ TRAY	TRAY/ CARTON	QUANTITY	GROSS WEIGHT	NET WEIGHT

MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD									
X." ±2"	X." ±2"										
.X ±0.30	.X ±0.012										
.XX ±0.20	.XX ±0.008										
.XXX ±0.10	.XXX ±0.004	TITLE		RJ45 8P8C 屏蔽 板上DIP 有柱 H13.20 黄绿LED				DR			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		PART NO.		109315141				CHKD			
		PRO J.		PAGE	2/2	UNITS	mm	APPD			
				SIZE	A4	SCALE	1:1	DIS NO.			