


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.03.20	阿树


MATERIAL 材料:
HOUSING 外壳: PBT,UL94V-0,BLACK.
TERMINALS BRACKET 端子支架: PBT,UL94V-0,BLACK.
SHIELD 保护物: C2680,T=0.20MM,NICKEL PLATING ON ALL AREA.
TERMINAL 端子: PHOSPHOR BRONZE C5210,T=0.35MM,
GOLD PLATING ON CONTACT AREA.

MECHANICAL 机械:
DURABILITY 耐用性: 750 CYCLES MIN.
MATING FORCE 配合力: 23N MAX.
OPERATING TEMPERATURE 工作温度: -40°C~+85°C.
STORAGE TEMPERATURE 储存温度: -40°C~+85°C.
ALL CRITICAL DIMENSIONS WITH "*"


Electrical 电气:
1.Turn ratio 匝数比:1~2:J1~J2=1CT:1CT(±2%).
3~4:J3~J6=1CT:1CT(±2%)
7~8:J4~J5=1CT:1CT(±2%)
9~10:J7~J8=1CT:1CT(±2%)
2.OCL:180uH Min.at 100KHz 100mV
3.Insertion Loss 插入损耗:-1.0 dB Max 1~125MHz.
4.Return loss 回波损耗:-20dB Min 1~40MHz.
-20+15LOG10(f/40MHz) Min 40~200MHz.
5.Cross talk: -30dB TYP 1~125MHz;
6.CMR:-30dB Min 30~200MHz;
7.Hi-Pot:2250V DC VRMS MIN AT 60 SECONDS




TOP VIEW




FRONT VIEW




BOTTOM VIEW




RIGHT SIDE VIEW




RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE



LEFT SIDE VIEW




BACK VIEW



X01AQ285AA2AD4A2

1:Au=1U"
3:Au=3U"
4:Au=6U"
5:Au=15U"
6:Au=30U"



LED Specification

Standard LED Color	LED Wavelength	Foward(A)	Foward(V)
Green	568nm	20mA	1.85~2.45V
Yellow	585nm	20mA	1.7~2.2V

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	RJ JACK
APPROVED		SIZE: A4	PART NO.: X01AQ285AA2AD4A2
			DWG NO.: X-X01AQ285AA2AD4A2

SCALE	PAGE	REVISION
N/A	1/1	A1