

	Doc. No.	SP-A0162-02	Page No.	1/7
	Date Issued	2026-03-23	Prepared by	AShu
	Date revised	2026-03-23	checked by	Sangshen
Product Specification	Rev. No.	A0	Approved by	Willy
Title : DIP SWITCH 拨码开关				

1. SCOPE (适用范围)

This specification covers the performance, tests and quality requirements for the DIP SWITCH.
(本规范涵盖了拨码开关的性能、测试和质量要求。)

2. PRODUCT DESCRIPTION (产品描述)

DESCRIPTION (描述)	Part Number (料号)
拨码开关,2.54mm,立插凸柄	DSIC01LH-P

3. APPLICABLE DOCUMENT (适用文件)

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence. (下列文件构成本规范的一部分，在此规定的范围内。本规范要求与产品图纸有冲突时，以产品图纸为准。如果本规范的要求与参考文件发生冲突，应以本规范为准。)

4. REQUIREMENTS (要求)

4.1. Design and Structure (设计和结构)

Product shall be of the design, structure and physical dimensions specified on the applicable product drawing. (产品的设计、结构和物理尺寸参考所适用的产品图纸)

4.2. Materials/ Finish (材料/表面处理)

Materials used in the structure of product shall be as specified on the applicable product drawing. (产品结构中使用的材料参考所适用的产品图纸)

	Doc. No.	SP-A0162-02	Page No.	2/7
	Date Issued	2026-03-23	Prepared by	AShu
	Date revised	2026-03-23	checked by	Sangshen
Product Specification	Rev. No.	A0	Approved by	Willy
Title : DIP SWITCH 拨码开关				

4.3. Ratings (额定功率)

Item (项目)	Standard (标准)
Rated Voltage (Maximum)额定电压	50V DC
Rated Current (Maximum)额定电流	0.5A
Operating temperature range工作温度范围	-20℃~+70℃ From -20 to +70 degree centigrade
Storage Temperature Range储存温度范围	-40℃~+85℃ From -40 to +85 degree centigrade

5. TEST STANDARD (测试条件)

5.1 Unless otherwise specified, the standard range of atmospheric conditions for making measurements and tests are as follows (除另有说明外，用以进行测量和测试的标准环境条件范围如下)

Ambient temperature (环境温度) : 5℃ to 35℃
Normal humidity (正常湿度) : 45% to 85%
Air pressure (气压) : 86Kpa to 106Kpa

5.2 However if doubt arises on the decision based on the measured Values under the above-mentioned Conditions.The following conditions shall be employed: (但是在对判定产生疑问时,按下述状态实施)

Temperature (温度) : 20±2℃
Relative humidity (相对湿度) : 65±5%
Air pressure (气压) : 86Kpa to 106Kpa

6. PERFORMANCE AND TEST DESCRIPTION (性能和测试类型)

6.1 APPEARANCE (外观)

ITEM	DESCRIPTION (类型)	TEST CONDITION (测试条件)	REQUIREMENT (要求)
1	Appearance (外观)	Visual. (目视)	Should not have any flaw Scratch discoloration and crushed (无任何裂痕、刮伤、 污染和变形)

	Doc. No.	SP-A0162-02	Page No.	3/7
	Date Issued	2026-03-23	Prepared by	AShu
	Date revised	2026-03-23	checked by	Sangshen
Product Specification	Rev. No.	A0	Approved by	Willy
Title : DIP SWITCH 拨码开关				

6.2 ELECTRICAL (电气)

ITEM	DESCRIPTION (类型)	TEST CONDITION (测试条件)	REQUIREMENT (要求)
2	Contact Resistance 接触电阻	1000Hz Measuerd at small current (100mA or less)1000Hz 在小电流(100 毫安或以下)1000 赫兹测试	初始值 Initial: 50mΩ Max 测试后 After test:100mΩ Max
3	Insulation Resistance 绝缘电阻	After 500 VDC for 1 minute, measure the insulation resistance between the adjacent contacts of mated and unmated connector assemblies. (使用500 V交流電 測試1分鐘，測量相邻两端的绝缘电阻)	100MΩ MIN.
4	Dielectric strength 耐电压	AC500V(50-60HZ,0.5mA current) being applied between all the adjacent terminals and between the terminal and frame for 1 minute (在接触端子或排 脚之间输入 500VAC(50-60 赫兹) 电压 1 分 钟，感应电流为 0.5mA	There shall be no breakdown. (无击穿、闪烁现象)

6.3 MECHANICAL (机械)

ITEM	DESCRIPTION (类型)	TEST CONDITION (测试条件)	REQUIREMENT (要求)
5	Operating force 作动力	Place the switch such that the direction of switch operation is vertical and then gradually increase the load applied to the center of the stem, the maximum load required for the stem to come to a stop shall be measured. (开关的动作方向为垂直放置开 关向推柄中心逐渐地增加负荷直到推柄停止 时所测量的最大负荷)	8N

	Doc. No.	SP-A0162-02	Page No.	4/7
	Date Issued	2026-03-23	Prepared by	AShu
	Date revised	2026-03-23	checked by	Sangshen
Product Specification	Rev. No.	A0	Approved by	Willy
Title : DIP SWITCH 拨码开关				

6	Displacement of actuator (knob) 推柄强度	Fixed switch so that the switch is perpendicular to the direction of operation and exerts 0.81 kgf force in the opposite direction of the push handle action. (固定开关, 使开关与操作方向垂直, 以推柄动作方向反方向施加 0.81 Kg f 力)	The handle is not seriously deformed and can work normally. (柄部无严重变形, 可以正常工作)
7	LIFE TEST 寿命试验	Endurance without loading: A switch shall be subjected to 2,000 cycles at a speed of 15 to 18 cycles per minute without loading. (无负荷: 在无负荷的条件下以每分钟 15~18 回的速度进行 2,000 次的测试)	(1) Contact Resistance (接触电阻): 100mΩ MAX. (2) Insulation resistance (绝缘电阻): 100M Ω MIN. (3) Dielectric strength (耐电压): AC 500V, 1 minute. (4) Operating force (作动力): 8N (5) Without damage to parts arcing or breakdown etc. (测试后外表无损伤, 并且满足机械性能)

6.4 ENVIRONMENTAL (环境)

ITEM	DESCRIPTION (类型)	TEST CONDITION (测试条件)	REQUIREMENT (要求)
8	Resistance to soldering heat 耐焊性试验	Solder bath method: solder temperature 260±10 °C immersion time 2±0.5 sec immersion depth up to the surface of the board thickness of printed wiring board 1.6mm dimensions of component holes in the printed wiring board shall be in accordance with those specified in this specification 焊炉焊接的时候温度控制在 260±10℃, 过炉时间 2±0.5 秒, 于(基板)厚度 1.6mm	No deformation of the housing. To meet the mechanical and electrical properties 本体无变形, 能满足于机械、电器性能

	Doc. No.	SP-A0162-02	Page No.	5/7
	Date Issued	2026-03-23	Prepared by	AShu
	Date revised	2026-03-23	checked by	Sangshen
Product Specification	Rev. No.	A0	Approved by	Willy
Title : DIP SWITCH 拨码开关				

9	Low Temperature test 低温试验	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for one hour before measurements are made: 样品按下列条件进行耐低温试验, 试验后在正常温度和湿度条件下放置 1 小时后测定 (1)Temperature 温度: $-20\pm 3^{\circ}\text{C}$ (2)Time 时间: 96 hours Water drops shall be removed.擦除水珠	No deformation of the housing. To meet the mechanical and electrical properties 本体无变形, 能满足于机械、电器性能
10	Heat Resistance 高温	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for one hour before measurements are made: 样品按下列条件进行耐热试验, 试验后在正常温度和湿度条件下放置 1 小时后测定 (1) Temperature 温度: $85\pm 2^{\circ}\text{C}$ (2) Time时间: 96 hours	No deformation of the housing. To meet the mechanical and electrical properties 本体无变形, 能满足于机械、电器性能
11	Salt Spray (盐水喷雾)	Based upon EIA-364-26A/MIL-STD-202 Method 101D Cond.B 24±1 hours exposure to a salt spray from the $5\pm 1\%$ solution at $35\pm 2^{\circ}\text{C}$. (在温度 $35\pm 2^{\circ}\text{C}$, 盐水浓度 $5\pm 1\%$下, 盐水喷雾 24±1 小时)	Appearance 外观 : No Damage 无异状 Contact Resistance 接触阻抗:100 mΩ Max.
12	Moisture Resistance (耐潮湿)	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for one hour before measurements are made: 样品按下列条件进行耐潮湿试验, 试验后在正常温度和湿度条件下放置 1 小时后测定 (1) Temperature 温度: $40\pm 2^{\circ}\text{C}$ (2) Relative humidity 相对湿度: 90 to 95% (3) Time 时间: 96hours Water drops shall be removed.擦除水珠	No deformation of the housing. To meet the mechanical and electrical properties 本体无变形, 能满足于机械、电器性能


7. SOLDERING AND CLEANING PROCESSES 焊接和清洗 :

7.1. Keep all switch contacts in their "OFF" position for all operations.

在所有操作过程中, 请确保开关在 OFF 位置

	Doc. No.	SP-A0162-02	Page No.	6/7
	Date Issued	2026-03-23	Prepared by	AShu
	Date revised	2026-03-23	checked by	Sangshen
Product Specification	Rev. No.	A0	Approved by	Willy
Title : DIP SWITCH 拨码开关				

- 7.2. Wave soldering (波峰焊) : DIP Suggestions solder temperature at 260℃(500°F) max.5 seconds . DIP 型推荐焊接焊锡温度为 260℃ (500°F) 最多 5 秒
- 7.3. Hand soldering (手焊) : Use a soldering iron of 30 watts controlled at 350℃ approximately 5 seconds. while applying solder.
使用 30W 烙铁控制温度在 350℃,焊接时长约 5 秒
- 7.4. Reflow soldering profile(回炉焊):When the maximum temperature of the reflow furnace is 260 °C and the temperature is 260 °c. 10 seconds MAX. (reference) SMT 型回焊炉最高温度为 260℃ , 温度为 260℃时 , 最长时间不超过 10 秒 (如图)



8. PACKAGING 包装

Please refer to the packing drawing. 请参考产品包装图纸

Rev.	Description	Date revised	Created/ Revised by
A0	New Release	2026/03/23	AShu