

50N06


N-CHANNEL POWER MOSFET

50A, 60V N-CHANNEL ENHANCEMENT MODE POWER MOSFET

DESCRIPTION

The 50N06 is an N-channel power MOSFET using our advanced technology to provide customers with a minimum on-state resistance and superior switching performance. The HY50N06A is generally applied in low power switching mode power appliances and electronic ballast.


The 50N06 meet the ROHS and Green Product requirement with full function reliability approved.



FEATURES

- * $R_{DS(ON)} \leq 15 \text{ m}\Omega$ @ $V_{GS}=10\text{V}$, $I_D=25\text{A}$
- $R_{DS(ON)} \leq 20 \text{ m}\Omega$ @ $V_{GS}=4.5\text{V}$, $I_D=25\text{A}$
- * High Switching Speed
- * Improved dv/dt capability

SYMBOL



ABSOLUTE MAXIMUM RATINGS($T_A=25^\circ\text{C}$, unless otherwise specified.)

SYMBOL	PARAMETER		VALUE	UNIT
V_{DSS}	Drain-Source Voltage		60	V
V_{GSS}	Gate-Source Voltage		± 20	V
I_D	Continuous Drain Current		50	A
I_{DM}	Pulsed Drain Current (Note 2)		100	A
EAS	Avalanche Energy (Note 3)	Single Pulsed	32	mJ
P_D	Power Dissipation	TO-220F	36	W
		TO-252	51	
T_j	Junction temperature		+150	$^\circ\text{C}$
T_{stg}	Operation and Storage Temperature		-55~+150	$^\circ\text{C}$
R_{θJA}	Thermal Resistance from Junction to Ambient (Note 6)	TO-220F	62.5	$^\circ\text{C/W}$
		TO-252	110	
R_{θJC}	Thermal Resistance From Junction To Case (Note 5)	TO-220F	3.47	$^\circ\text{C/W}$
		TO-252	2.45	

- Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.
2. Repetitive Rating: Pulse width limited by maximum junction temperature.
3. $L=0.1\text{mH}$, $I_{AS}=25\text{A}$, $V_{DD}=30\text{V}$, $R_G=20\Omega$, Starting $T_J=25^\circ\text{C}$
4. $I_{SD} \leq 30\text{A}$, $di/dt \leq 200\text{A}/\mu\text{s}$, $V_{DD} \leq B_{VDSS}$, Starting $T_J=25^\circ\text{C}$
5. Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.

50N06

N-CHANNEL POWER MOSFET

■ ELECTRICAL CHARACTERISTICS (TA=25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFF CHARACTERISTICS						
Drain-Source Breakdown Voltage	BVDSS	VGS=0V, ID=250μA	60			V
Drain-Source Leakage Current	IDSS	VDS=60V,VGS=0V			10	μA
Gate- Source Leakage Current	IGSS	VGS=±20V, VDS=0V			±100	nA
ON CHARACTERISTICS						
Gate Threshold Voltage	VGS(TH)	VDS=VGS , ID=250μA	1.0		3.0	V
Static Drain-Source On-State Resistance	RDS(ON)	VGS=10V, ID=25A		14	18	mΩ
DYNAMIC CHARACTERISTICS						
Input Capacitance	CISS	VDS=25V, VGS=0V, f= 1.0MHz		2315		pF
Output Capacitance	COSS			181		
Reverse Transfer Capacitance	CRSS			144		
SWITCHING CHARACTERISTICS						
Total Gate Charge	QG	VDS=48V,VGS= 10V, ID=50A (Note1, 2)		56		nC
Gate-Source Charge	QGS			8.4		
Gate-Drain Charge	QGD			16		
Turn-on delay time	td(on)	VDS=30V,ID=50A VGS=10V,RG=6Ω (Note1, 2)		9		ns
Turn-on rise time	tr			18		
Turn-off delay time	td(off)			54		
Turn-off fall time	tf			28		
DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS						
Maximum Continuous Drain-Source Diode Forward Current	IS				50	A
Maximum Pulsed Drain-Source Diode Forward Current	ISM				100	A
Drain-source diode forward voltage	VSD	IS=50A, VGS=0V			1.5	V
Reverse Recovery Time	trr	Is = 30A,VGS = 0V dIs/dt = 100A/μs		60		ns
Reverse Recovery Charge	Qrr			30		nC


Notes:

1. Pulse Test : Pulse Width≤300μs, duty cycle ≤2%.
2. Essentially independent of operating temperature.


50N06

N-CHANNEL POWER MOSFET

■ TEST CIRCUITS AND WAVEFORMS



Peak Diode Recovery dv/dt Test Circuit



Peak Diode Recovery dv/dt Waveforms

50N06

N-CHANNEL POWER MOSFET

■ TEST CIRCUITS AND WAVEFORMS(Con.t)




Fig. 2A Switching Test Circuit




Fig. 2B Switching Waveforms




Fig. 3A Gate Charge Test Circuit




Fig. 3B Gate Charge Waveform




Fig. 4A Unclamped Inductive Switching Test Circuit










Fig. 4B Unclamped Inductive Switching Waveforms







50N06

N-CHANNEL POWER MOSFET

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS



Technical drawing of a mechanical part showing dimensions: 7.0°, R0.15, 2.3±0.1, and 6.6±0.1.

Page :7