






SECTION A-A

SCALE 1:1



Specifications

A. Material

Insulator: PA9T, UL94 V-0, Black
Contact: Copper Alloy, T=0.25mm
Mid Plate: Stainless Steel, T=0.20mm
Shell: Stainless Steel, T=0.30mm
Inner Shell: Stainless Steel, T=0.20mm
Weld Plate: Stainless Steel, T=0.15mm

B. Plating

Contact Area: 3u" Au over 60u" min. Nickel
Solder Tails: Gold Flash Au over 60u" min. Nickel
Shell: Gold Flash Au over 60u" min. Nickel
Inner Shell: No Plating
Mid Plate: 50u" min. Nickel
Weld Plate: No Plating

C. Electrical

Current Rating: 5.00A collectively for VBus & GND pins
1.25A for A5/B5 pins
0.25A for all other pins

Voltage Rating: 48V

Power Rating: 240W

Contact Resistance: 40mΩ max initial
50mΩ max after test

Dielectric Withstanding Voltage: 100V AC

Insulation Resistance: 100MΩ min.

D. Mechanical & Environmental

Operating Temperature: -25℃ to +85℃

Mating Force: 5 to 20 N.

Unmated Force: 6 to 20 N after test


Durability: 10,000 cycles

Part Number			Product Description		
PTCFW-H22A-086			USB 2.0 Type C Receptacle, Horizontal, SMT, Mid Mount, IP67, 16 Pin		
DWG.No.	P-TCF-120		Tolerances Unspecified		Units: Metric(mm)
Revision	A0		X.X ±0.35	X° ±5°	
Designed	Lee	12/15/20	X.XX ±0.25	X.X° ±2°	
Approved	Allen	12/15/20	X.XXX ±0.15		



www.szywf.com.cn
www.szywf.cn


Sheet No. 1/3





RECOMMENDED PCB LAYOUT(COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ± 0.05

PIN ASSIGNMENTS





PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SUB2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND




Part Number			Product Description				 www.szywf.com.cn www.szywf.cn	
PTCFW-H22A-086			USB 2.0 Type C Receptacle, Horizontal, SMT, Mid Mount, IP67, 16 Pin					
DWG.No.	P-TCF-120		Tolerances Unspecified			Units: Metric(mm)		
Revision	A0		X.X	±0.35	X°	±5°		
Designed	Lee	12/15/20	X.XX	±0.25	X.X°	±2°		
Approved	Allen	12/15/20	X.XXX	±0.15				
							Sheet No. 2/3	



SEE DETAIL X



Part Number			Product Description			 Connecting the Future www.szywf.com.cn www.szywf.cn	
PTCFW-H22A-086			USB 2.0 Type C Receptacle, Horizontal, SMT, Mid Mount, IP67, 16 Pin				
DWG.No.	P-TCF-120		Tolerances Unspecified		Units: Metric(mm)		ROHS COMPLIANT 2011/65/EU Deca-BDEV
Revision	A0		X.X ±0.35	X° ±5°			
Designed	Lee	12/15/20	X.XX ±0.25	X.X° ±2°			
Approved	Allen	12/15/20	X.XXX ±0.15				
Sheet No. 3/3							

	REEL	CARTON
QUANTITY (PCS)	1300	13000