





X1004-H-2x15-N0          

①            ②            ③            ④

- | PIN  | DIM.(MM) |       |
|------|----------|-------|
|      | A        | B     |
| 2X08 | 7.00     | 9.70  |
| 2X10 | 9.00     | 11.70 |
| 2X15 | 14.00    | 16.70 |
| 2X16 | 15.00    | 17.70 |
| 2X20 | 19.00    | 21.70 |
| 2X25 | 24.00    | 26.70 |

|                  |             |      |         |          |           |      |                        |  |      |                                      |                                                                                             |                                               |                |              |                |
|------------------|-------------|------|---------|----------|-----------|------|------------------------|--|------|--------------------------------------|---------------------------------------------------------------------------------------------|-----------------------------------------------|----------------|--------------|----------------|
|                  |             |      |         |          |           |      | DSND                   |  | DATE |                                      | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.54 mm Crimp Style Connectors |                |              |                |
|                  |             |      |         | XKB      | ANGLAR    | ±5°  | DWN                    |  | DATE |                                      | VIEW:  | PART NO.:<br><b>X1004H-2x15-N0</b>            |                |              |                |
| ΔX               |             |      |         |          | L ≤ 4     | ±0.2 | CHKD                   |  | DATE |                                      | UNIT: mm/in                                                                                 | DWG NO.:<br><b>X-X1004H-2x15-N0</b>           |                |              |                |
| ΔX               |             |      |         |          | 4<L ≤ 16  | ±0.3 | APPD                   |  | DATE |                                      | SIZE: A4                                                                                    |                                               |                |              |                |
| ΔX               |             |      |         |          | 16<L ≤ 63 | ±0.4 |                        |  |      |                                      |                                                                                             |                                               |                |              |                |
| MARK             | DESCRIPTION | DATE | REVISED | APPROVED | L > 63    | ±0.5 |                        |  |      |                                      |                                                                                             |                                               |                |              |                |
| REVISIONS        |             |      |         |          |           |      | UNSPECIFIED TOLERANCES |  |      | XKB INDUSTRIAL PRECISION CO.,LIMITED |                                                                                             |                                               | WEIGHT<br>1.0g | SHEET<br>1/1 | REVISION<br>A0 |
| www.helloxkb.com |             |      |         |          |           |      |                        |  |      |                                      |                                                                                             |                                               |                |              |                |