







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.16	阿树



规格 Specification

*电气特性 Electrical Characteristics:

触点额定电流 Contact Current Rating: 0.5Amperes.
 耐压 Dielectric Withstanding Voltage: AC500V r.m.s.
 绝缘电阻 Insulation Resistance: 1000 Megohms
 Minimum At DC 500V.

接触电阻 Contact Resistance: 100 mΩ Maximum.

*机械特性 Mechanical Characteristics:

寿命 Mating Cycles: 10,000 Cycles.

*环境 Environmental:

工作温度 Operating Temperature: -25°C~+85°C.

*材料 Materials:

绝缘子 Insulator: HI-Temp plastic UL 94V-0 Rated.

触点 Contact: Copper Alloy.

外壳 Shell: Stainless Steel (t=0.15mm).



PAD AREA



NO COPPER AREA

Pin	Define
P1	SWITCH TERM CD
P2	DAT1
P3	DATO
P4	VSS
P5	CLK
P6	VDD
P7	CMD
P8	CD/DAT3
P9	DAT2
P10	GND
P11	GND
P12	GND

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	TF CARD CONN
APPROVED		SIZE: A4	PART NO.: XKTF-1230-51
			DWG NO.: X-XKTF-1230-51
SCALE	PAGE	REVISION	
N/A	1/1	A1	