





07~09 Pin



10~16 Pin

Specifications:

规格:  
**Voltage rating:**100V AC/DC  
 额定电压: 100V AC/DC  
**Current rating:**3A AC/DC  
 额定电流: 3A AC/DC  
**Withstanding voltage:**800V AC/minute  
 耐受电压: 800V AC/分钟  
**Temperature range:**-25℃~+85℃  
 温度范围: -25℃~+85℃  
**Insulation resistance:**1000MΩ min  
 绝缘电阻: 1000MΩ Min  
**Contact resistance:**20mΩ Max  
 接触电阻: 20mΩ Max

| X2000 | W | V | - 11 | - N0 | SN |
|-------|---|---|------|------|----|
| ①     | ② | ③ | ④    | ⑤    | ⑥  |

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:XX-02~16P
- 5.Material:N0-PA66 UL94V-0
- 6.Plating:SN-Tin Plated

| Poles | Dimensions(mm) |       | Poles | Dimensions(mm) |       |
|-------|----------------|-------|-------|----------------|-------|
|       | A              | B     |       | A              | B     |
| 02    | 2.00           | 6.00  | 08    | 14.00          | 18.00 |
| 03    | 4.00           | 8.00  | 09    | 16.00          | 20.00 |
| 04    | 6.00           | 10.00 | 10    | 18.00          | 22.00 |
| 05    | 8.00           | 12.00 | 11    | 20.00          | 24.00 |
| 06    | 10.00          | 14.00 | 12    | 22.00          | 26.00 |
| 07    | 12.00          | 16.00 | 16    | 30.00          | 34.00 |

|                 |          |               |                      |
|-----------------|----------|---------------|----------------------|
| X2000WV-11-N0SN | PA66     | Brass         | X2000H               |
| PART NO         | Material | Material(Pin) | Suitable XKB Housing |

| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|
| ΔX                                            |             |      |         |          | ANGLAR ±5°             |
| ΔX                                            |             |      |         |          | L≤ 4 ±0.2              |
| ΔX                                            |             |      |         |          | 4<L≤ 16 ±0.3           |
| ΔX                                            |             |      |         |          | 16<L≤ 63 ±0.4          |
| ΔX                                            |             |      |         |          | L> 63 ±0.5             |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |



XKB INDUSTRIAL PRECISION CO.,LIMITED

|                       |  |                                                                                             |                                            |       |          |
|-----------------------|--|---------------------------------------------------------------------------------------------|--------------------------------------------|-------|----------|
| DSND                  |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.0mm Crimp Style Connector |       |          |
| DWN                   |  | VIEW:  | PART NO.:<br>X2000WV-11-N0SN               |       |          |
| CHKD                  |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X2000WV-11-N0SN              |       |          |
| APPD                  |  | SIZE: A4                                                                                    |                                            |       |          |
| PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                                     | SHEET | REVISION |
|                       |  |                                                                                             |                                            | 1/1   | A0       |