






SECTION A-A
SCALE 1:1



Specifications

A.Material

Insulator: LCP, UL 94V-0, Black
Contact: Copper Alloy, T=0.12mm
Mid Plate: Stainless Steel, T=0.15mm
Shell: Stainless Steel, T=0.30mm

B.Plating

Contact Area: Gold Flash, 30u"min Nickel Base.
Solder Tails Area: Gold Flash, 30u"min Nickel Base.
Shell: 30u" min Nickel.
Mid Plate: No Plating .

C.Electrical

Current Rating:
3.00A collectively for VBus for GND pins
1.25A for A5/B5 pin
0.25A per pin for all other pins
Voltage Rating: 48V
Power Rating: 240W
Contact Resistance: 40mΩ max initial.
50mΩ max after test
Dielectric Withstanding Voltage: 100V AC
Insulation Resistance 100MΩ min

D.Mechanical & Environmental


Operating Temperature: -25°C to +85°C
Mating Force: 5 to 20 N.
Unmated Force: 6 to 20 N after test
Durability: 10,000 cycles

Part Number			Product Description				 www.szywf.com.cn www.szywf.cn
PTCFW-H22A-115			USB 2.0 Type C Receptacle, Horizontal, SMT, PCB Top Mount, 16 Pin				
DWG.No.	P-TCF-113		Tolerances Unspecified		Units: Metric(mm)		
Revision	A0		X.X ±0.35	X° ±5°	 		
Designed	Lee	11/30/20	X.XX ±0.25	X.X° ±2°			
Approved	Allen	11/30/20	X.XXX ±0.15				



www.szywf.com.cn
www.szywf.cn


Sheet No. 1/3




RECOMMEND P.C.B LAYOUT(COMPONENT SIDE)
TOLERANCE FOR PCB LAYOUT IS ± 0.05

PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SUB2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND




Part Number			Product Description			 <i>Connecting the Future</i> www.szywz.com.cn www.szywz.cn
PTCFW-H22A-115			USB 2.0 Type C Receptacle, Horizontal, SMT, PCB Top Mount, 16 Pin			
DWG.No.	P-TCF-113		Tolerances Unspecified		Units: Metric(mm)	
Revision	A0		X.X ±0.35	X° ±5°		
Designed	Lee	11/30/20	X.XX ±0.25	X.X° ±2°		
Approved	Allen	11/30/20	X.XXX ±0.15			
						Sheet No. 2/3







www.szywf.com.cn
www.szywf.cn

Sheet No. 2/3




SEE DETAIL X



	REEL	CARTON
QUANTITY (PCS)	1200	12000

Part Number			Product Description		
PTCFW-H22A-115			USB 2.0 Type C Receptacle, Horizontal, SMT, PCB Top Mount, 16 Pin		
DWG.No.	P-TCF-113		Tolerances Unspecified		
Revision	A0		X.X	±0.35	X° ±5°
Designed	Lee	11/30/20	X.XX	±0.25	X.X° ±2°
Approved	Allen	11/30/20	X.XXX	±0.15	

Units:
Metric(mm)



www.szywf.com.cn
www.szywf.cn

Sheet No. 3/3