









SPECIFICATION:

1. Material

Housing Material:High temperature thermoplastic

Contact Terminal:High Grade Copper Alloy

Merallic Shell:Stainless Steel

Inner Ground Cover Shell:Stainless Steel

Mid Plate:Stainless Steel

2. Mechanical:

2.1.Mating force:5-20Nf;

2.2.Unmating force:Initial:8-20Nf;Final:6-20Nf;

2.3.Durability:5000 Cycles;

3. Electrical:

3.1.Current Rating:3A

3.2.Voltage Rating:20V Max.;

3.3.Dielectric Withstanding

volage:100Vac,60S,10mA;

3.4.Contact resistance:40m Ohms Max.;


3.5.Insulation Resistance:100M Ohms Min.;

4.Environmental:

4.1.Operating temperature:-40°C~+85°C;

4.2.Salt Spray Test:24H Min.(No oxidation or rust);

U262-161N-4BC20865



MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGLAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
Δx					16 < L ≤ 63 ±0.4
Δx					L > 63 ±0.5
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: Type-C 3.1
DWN		VIEW:	PART NO.: U262-161N-4BC20865
CHKD		UNIT: mm/in	DWG NO.: X-U262-161N-4BC20865
APPD		SIZE: A4	WEIGHT SHEET REVISION
			1/1 A0