


	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		独立各PIN数图纸, 增加开孔定位尺寸	2024.12.11	阿树
A2	ECN-P-2026010902	A2 X1	产品尺寸变更	2026.01.09	阿树



PART NO.:

X06 26 F I 7 B 2
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Pin No.:26PIN
③Welding Board Angle :F—Female
④T: Tradutional
⑤Planting Category:
1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn
⑥Color:B:Black W:White BL:Blue Y:Yellow G:Green R:Red
⑦1:TYPE—1; 2:TYPE—2; 3:TYPE—3; 6:TYPE—6

Specifications:

规格:

Current rating:5A AC/DC

额定电流: 5A AC/DC

Voltage rating:500V AC

额定电压: 500V AC

Withstanding voltage:500V AC/MIN

耐受电压: $\geq 500V$ AC/分钟

Temperature range: -55°C $- +105^{\circ}\text{C}$

温度范围: $-55^{\circ}\text{C}-+105^{\circ}\text{C}$

Insulation resistance:1000MΩMIN

绝缘电阻: $\geq 1000\text{M}\Omega$

Contact resistance:30mΩMAN

接触电阻: $\leq 30\text{m}\Omega$

Material And FINISHED:

材料和成本:

INSULATOR:PBT+30% GF UL 94V-0



绝缘体: PBT+30% GF UL 94V-0

SHELL: Steel Plated Ni

外壳: 钢 镀镍

CONTACT MATERIAL:Brass

触点材料：黄铜



铆合方式	TYPE-1: 铆合	TYPE-6: 直铆锁	TYPE-3: 叉锁	TYPE-2: 铆合锁螺丝
图式				

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED	TOLERAUCES

XKIB 星城 Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X0626FT7B2
APPROVED		SIZE: A4	DWG NO.: X-X0626FT7B2

SCALE	PAGE	REVISION
N/A	1/1	A2