



浙江领强电子科技有限公司
Zhejiang Linqiang Electronic Technology Co.,Ltd.
产 品 承 认 书
Product acknowledgement

产 品 承 認 書

Productacknowledgment

客户 (Customer) :

品 名 (Product Name) : 连接器

料号 (Material number) : GH系列

本公司确认Our confirmation		
工程/日期engineering/date	业务/日期business/date	批准/日期Approval/date
周少华 2020.05.04	赵先礼 2020.05.04	田泽民 2020.05.04
客户确认Customer confirmation		
工程/日期engineering/date	品质/日期quality/date	批准/日期Approval/date

[illegible]

[illegible]


浙江领强电子科技有限公司 Zhejiang Linqiang Electronic Technology Co.,Ltd. 产 品 承 认 书 Product acknowledgement	产品名称 product name	接插件 connectors
	产品型号 Product model	GH卧贴/立贴
	版本号 Version No	1版 1 version
	页码 Page number	共8页 第4页 Page 4 of 8
1. 适用范围 Scope of application 本规范适用于GH系列产品。 This specification is applicable to GH series products		
2. 标准额定值 Standard rating		
项目 project	规格 specifications	
额定电压 The rated voltage	50V AC/DC	
额定电流 Rated current	1.0A AC/DC	
使用温度范围 Operating temperature range	-40℃～+105℃	
使用湿度范围 Operating humidity range	相对湿度90%以下 Relative humidity is below 90%	
3. 环保 The environmental protection 产品符合ROHS环保要求。Products in line with ROHS environmental protection requirements.		
4. 包装 Packing 产品内包装为连带，外包装为纸箱，产品在箱内密封，不晃动。 The inner packing of the product is joint and several, the outer packing is carton, the product is sealed in the box, do not shake.		
5. 运输 transport 允许用任何方式运输，但需避免雨雪淋和阳光照射，不能有碰撞和挤压等机械损伤，运输环境温度为-20℃+50℃ It is allowed to be transported by any means, but it should avoid rain, snow and sunlight, no mechanical damage such as collision and extrusion, and the ambient temperature of transportation is -20℃+50℃		
6. 贮存: Storage 包装完毕连接器应在环境温度为-20℃～+50℃，相对湿度不大于90%，周围空气中没有酸性，碱性及其它腐蚀性气体的仓库中贮存。 After packaging, the connector should be in the ambient temperature of -20℃～+50℃, the relative humidity should not be more than 90%, there is no acid, alkaline and other decay in the surrounding air Storage of corrosive gases in a warehouse.		
7. 部件名称/部件规格型号/部件材质 Part name/part specification/part material		
部件名称 Part name	型号 model	材质 The material
基座 base	GH	Vicryst R8535
插针 pin	GH	磷铜 Phosphor copper
固定片 stator	GH	磷铜 Phosphor copper
盖板	GH	
8. 外观及尺寸 Appearance and size		
8.1外观 appearance 塑胶件表面应无明显疤痕、杂色、开裂、毛刺、飞边、缺料及影响使用的变形；金属件表面应光洁、无锈蚀、氧化、脱皮、发黑及明显的机械损伤等缺陷。 The surface of plastic parts shall be free of obvious scars, mottled, cracked, burr, flash, lack of material and deformation affecting the use; the surface of metal parts shall be smooth and clean No rust, oxidation, peeling, blackening and obvious mechanical damage.		
8.2 尺寸 size 参照工程图 Reference engineering drawing		

浙江领强电子科技有限公司 Zhejiang Linqiang Electronic Technology Co.,Ltd. 产 品 承 认 书 Product acknowledgement		产品名称 product name	接插件 connectors
		产品型号 Product model	GH卧贴/立贴
		版本号 Version No	1版 1 version
		页码 Page number	共8页 第5页 Page 5 of 8
9. 电气特性 Electrical characteristics			
编号 number	项目 project	试验方法 Test method for	性能要求 performance requirements
9.1	接触电阻 contact resistance	将连接器插合，用接触电阻仪进行测试，测量连接器两个端子之间组成一个闭合的回路。 Plug in the connector and test it with a contact resistance meter to measure both terminals of the connector Form a closed loop between.	20mΩ Max
9.2	绝缘电阻 Insulation resistance	将连接器插合，在相邻接触件之间和接触件与外壳之间施加100V DC电压，持续1分钟进行测试。 Plug in the connector and apply 100V DC voltage between the adjacent contacts and between the contacts and the enclosure for 1 minute.	500MΩ Min
9.3	耐电压 Withstand voltage	将连接器插合，在相邻接触件之间和接触件与外壳之间施加500V AC电压，持续1分钟进行测试。 Plug in the connector and apply 500V AC voltage between the adjacent contacts and between the contacts and the enclosure for 1 minute.	无击穿和飞弧现象 No breakdown and flashover
10. 环境特性			
编号 number	项目 project	试验方法 Test method for	性能要求 performance requirements
10.1	耐热试验 Heating test	将插合连接器放在温度为+105℃±2℃的环境中96H,取出放在正常环境中1~2H后再进行测试。 Put the plug connector in the environment of +105℃±2℃ for 96H, take it out and put it in the normal environment for 1~2H before testing.	外观：外观无损伤 Appearance: appearance without damage
			接触电阻：30mΩ Max Contact resistance: 30mΩ Max
10.2	耐冷试验 Cold tolerance test	将插合连接器放在温度为-40℃±2℃的环境中96H,取出放在正常环境中1~2H后再进行测试。 The plug connector was placed in the environment with the temperature of -40℃±2℃ for 96H, and was taken out and placed in the normal environment for 1~2H before being tested.	外观：外观无损伤 Appearance: appearance without damage
			接触电阻：30mΩ Max Contact resistance: 30mΩ Max
10.3	耐湿性试验 Moisture resistance test	将插合连接器放在温度为40℃±2℃，相对湿度90~96%的环境中，持续96H,经试验后，取出放在正常环境中1~2H后再进行测试。 Place the plug connector in an environment with a temperature of 40℃±2℃ and relative humidity of 90~96%.Last for 96H, after the test, take it out and put it in the normal environment for 1~2H before the test.	外观：外观无损伤 Appearance: appearance without damage
			绝缘电阻：150MΩ MIN Insulation resistance: 150MΩ min
			耐电压符合9.3要求 Withstand voltage meets 9.3 requirements





浙江领强电子科技有限公司 Zhejiang Linqiang Electronic Technology Co.,Ltd. 产品承认书 Product acknowledgement		产品名称	接插件
		product name	connectors
		产品型号	GH卧贴/立贴
		Product model	
		版本号	1版
		Version No	1 version
		页码	共8页 第6页
		Page number	Page 6 of 8
编号	项目	试验方法	性能要求
number	project	Test method for	performance requirement
10.4	温度循环 Temperature cycle	把试验样品分别放入高低温试验箱，按下列步骤调试温度： a. 在-40℃±2℃的恒温条件下放置30分钟 b. 在常温条件下放置1H C. 在+105℃±2℃的恒温条件下放置30分钟 D. 在常温条件下放置1H 从a到d为一个循环周期，共进行5个循环，在正常环境中恢复2H后进行检查。 Put the test samples into the high and low temperature test chamber, and adjust the temperature according to the following steps: A. Place for 30 minutes under the constant temperature of -40℃±2℃ B. Place at room temperature for 1 hour C. Place for 30 minutes at a constant temperature of +105℃±2℃ D. Place at room temperature for 1 hour From a to d is a cycle period, a total of 5 cycles are carried out, and 2H is recovered in the normal environmentCheck later.	外观：无任何异状
			接触电阻：30mΩ Max Contact resistance: 30mΩ Max
10.5	盐雾试验 Salt Spray Test	将试验样品从试验箱顶悬挂下来，采用浓度为（5±1）%的氯化钠溶液，连续喷雾24H,试验后用流动的蒸溜水轻轻洗去表面沉淀积物，在常温条件下恢复1~2H后再检查测量。 The test sample was suspended from the top of the test box, and the concentration of (5±1)% Sodium Chloride Solution was continuously sprayed with 24H. After testing, the surface precipitates were lightly washed with flowing steaming water, then the 1~2H was rechecked at normal temperature.	外观：无损伤、腐蚀 （五金件应无露出底金属的严重锈蚀：使用预镀好的型材，其落料面允许有不影响其性能的轻微腐蚀。 Appearance: no damage or corrosion (hardware should not expose the bottom metal of serious corrosion: use pre-platingThe blanking surface is allowed to have a slight corrosion that does not affect its performance.
			接触电阻：30mΩ Max Contact resistance: 30mΩ Max

浙江领强电子科技有限公司 Zhejiang Linqiang Electronic Technology Co.,Ltd. 产 品 承 认 书 Product acknowledgement	产品名称 product name	接插件 connectors
	产品型号 Product model	GH卧贴/立贴
	版本号 Version No	1版 1 version
	页码 Page number	共8页 第7页 Page 7 of 8


编号 number	项目 project	试验方法 Test method for	性能要求 performance requirement
10.6	可焊性 weldability	把试验样品需要焊接的部位浸入240±5℃的锡溶液中，保持2.5±0.5秒。 Dip the welded part of the test sample into 240±5℃tin solution and hold 2.5±0.5 seconds.	沾锡面积95%以上 Tin area above 95%
10.7	耐焊性 Soldering resistance	将连接器置于PCB板上，然后将产品通过260℃±5℃回流焊或波峰焊5±1S进行测试。 Place the connector on the PCB, and then reflow the product through 260℃±5℃ Or wave soldering for 5±1s.	1. 塑胶件不得有明显变形损坏起泡。 2. 电气特性必须符合规格。 Plastic parts shall be free from obvious deformation, damage and blistering. 2. The electrical characteristics must meet the specifications.



浙江领强电子科技有限公司 Zhejiang Linqiang Electronic Technology Co.,Ltd. 产 品 承 认 书 Product acknowledgement					产 品 名 称 product name		接 插 件 connectors		
					产 品 型 号 Product model		GH卧贴/立贴		
					版 本 号 Version No		1版 1 version		
					页 码 Page number		共8页 第8页 Page 8 of 8		
11. 机械特性 mechanical properties									
编 号 number		项 目 project		试 验 方 法 Test method for				性 能 要 求 performance requirement	
11.1		PIN针固定力 Pin fixing force		将针座固定在插拔力机上，在针脚前端施加力，以每分钟25±3mm的速率，直到针退出针座的拔出力。 Fix the pin holder on the drawing machine and apply force on the front end of the pin at a rate of 25±3mm per minute until the pin is withdrawn from the pin holder.				单一PIN针 3N Min Single pin 5N min	
11.2		端子在塑胶件中保持力 Terminal retention in plastic parts		端子与孔座配合，以每分钟25±3mm的速率沿导线方向，将端子从孔座中拔出的力。 The terminal shall be matched with the hole seat, and at the rate of 25±3mm per minute along the conductor direction, theThe force that the terminal is pulled out of the socket.				单一端子： 7N Min Single terminal: 7N min	
11.3		机械寿命 Mechanical life		无通电状态下，10次/分钟的速度插拔30次。 Under no power on state, plug and unplug 30 times at the speed of 10 times / min.				接触电阻： 30mΩ Max Contact resistance: 30mΩ Max	
11.5		插入力拔出力 Insertion pull out force		试验方法：Test methods (1) 将孔座和端子配合好，与针座在同一轴线上进行插拔测试，测试时需将孔座锁扣去掉。（测试速度：20±5mm）minute (1) Fit the hole seat and the terminal, and conduct the insertion and removal test on the same axis with the needle seat. Remove the lock of the hole seat (test speed: 20 ± 5mm) minute during the test (2) 性能要求:Performance requirements					
				孔 位	插入(N) insert (max)	拔 出 (N) Pull out (min)	孔 位	插入(N) insert (max)	拔 出 (N) Pull out (min)
				2PIN	19.5	4.0	10PIN	69.5	8.0
				3PIN	29.5	4.5	11PIN	69.5	8.5
				4PIN	39.5	5.0	12PIN	69.5	9.0
				5PIN	49.5	5.5	13PIN	69.5	9.5
				6PIN	59.5	6.0	14PIN	69.5	10.0
				7PIN	69.5	6.5	15PIN	69.5	10.5
				8PIN	69.5	7.0	16PIN	69.5	11.0
				9PIN	69.5	7.5			



- 备注:
1. 材料: 载带PS 雾透色 $t=0.3$
热封/自粘上盖带: PET $t=0.05\text{mm}$.
纸箱: 纤维板、波纹、双堵、黄色。
卷盘: 聚苯乙烯, 耐热温度: 70°C , 蓝色。
 2. PET膜剥离力: $30\sim70\text{g}$, 剥离速度: 300mm/分钟 。
 3. 带子前后预留:



载带尺寸			载带尺寸			载带包封规格表		
Circuits	W	B0	F	Circuits	A	B0	F	PIR值
GH1.25-2P	16.0	6.10	7.50	GH1.25-12P	32.0	18.6	14.2	0.02-0.04P
GH1.25-3P	16.0	7.35	7.50	GH1.25-13P	32.0	19.85	14.2	0.02-0.04P
GH1.25-4P	16.0	8.60	7.50	GH1.25-14P	32.0	21.10	14.2	0.02-0.04P
GH1.25-5P	24.0	9.85	11.50	GH1.25-15P	44.0	22.35	20.2	0.02-0.04P
GH1.25-6P	24.0	11.10	11.50	GH1.25-16P	44.0	23.60	20.2	0.02-0.04P
GH1.25-7P	24.0	12.35	11.50					
GH1.25-8P	24.0	13.60	11.50					
GH1.25-9P	24.0	14.85	11.50					
GH1.25-10P	24.0	16.10	11.50					
GH1.25-11P	32.0	17.35	14.20					

BCN NO	标记	变更内容	签名	日期
--------	----	------	----	----

更改记录

品名	连接图	型号	GH1.25立贴型封装图
----	-----	----	--------------

X.X	±0.30	单位	mm	版本	A	审核/日期	周少华 2019.09.12
X.XX	±0.20	比例	1:1	共1页	第1页	批准/日期	田泽民 2019.09.12
X.XXX	±0.10						
Angle	±3.0°						

浙江领强电子科技有限公司