












PCB LAYOUT





Specifications:
规格：
Voltage rating:250V AC/DC
额定电压：250V AC/DC
Current rating:7A AC/DC
额定电流：7A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压：1500V AC/分钟
Temperature range:-25℃-+85℃
温度范围：-25℃-+85℃
Insulation resistance:1000MΩ min
绝缘电阻：1000MΩ Min
Contact resistance:20mΩ Max
接触电阻：20mΩ Max

X9396	W	V - 02	S-	N0	SN
①	②	③④	⑤	⑥	⑦

1.Series No
2.Category:W-Wafer
3.Welding Board Angle:V-Stright 180°
4.Row No.Pin No:XX-02~15P
5.Category:S-With positioning column
6Material:N0-PA66 UL94V-0
7.Plating:SN-Tin Plated

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.9600	9.8000	09	31.6800	37.5200
03	7.9200	13.7600	10	35.6400	41.4800
04	11.8800	17.7200	11	39.6000	45.4400
05	15.8400	21.6800	12	43.5600	49.4000
06	19.8000	25.6400	13	47.5200	53.3600
07	23.7600	29.6000	14	51.4800	57.3200
08	27.7200	33.5600	15	55.4400	61.2800

X9396WV-02S-N0SN	PA66	Brass	X9396H
PART N0	Material	Material(Pin)	Suitable XKB Housing

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS

ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 3.96mm Crimp Style Connector
DWN		VIEW:	PART NO.: X9396WV-02S-N0SN
CHKD		UNIT: mm/in	DWG NO.: X-X9396WV-02S-N0SN
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0