









PCB CUTOUT PANEL THICKNESS 1.27



Specifications:
规格: **XKB**
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:7A AC/DC
额定电流: 7A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤10mΩ
接触电阻: ≤10mΩ
After environmental test:≤20mΩ
环境测试后: ≤20兆欧

X9357 H M -2x04 B-N0
① ② ③ ④ ⑤ ⑥ ⑦

- 01 Series No.
- 02 Category:H-HSG
- 03 Welding Board Angle:M-Male HGS
- 04 Row No-Pin No.:2*XX-Double row
- 05 Plug the Pin & special No.B-With the back seat
- 06 Material:
- 07 Color:Blank-natural color

Poles	Dimensions(mm)				
	A	B	C	D	E
4	4.20	40.20	29.20	17.60	12.90
6	8.40	44.40	33.40	21.80	17.10
8	12.60	48.60	37.60	26.00	21.30
10	16.80	52.80	41.80	30.20	25.50
12	21.00	57.00	46.00	34.40	29.70
14	25.20	61.20	50.20	38.60	33.90
16	29.40	65.40	54.40	42.80	38.10
18	33.60	69.60	58.60	47.00	42.30
20	37.80	73.80	62.80	51.20	46.50
22	42.00	78.00	67.00	55.40	50.70
24	46.20	82.20	71.20	59.60	54.90
36	71.40	107.40	96.40	81.50	76.78

X9357HM-2x04B-N0	Nylon 66 94V-0	X9357TF	X9357HF-B
PART N0	Material	Suitable XBK Terminal	Suitable XBK Housing

				XKB	DSND		DATE		SCALE: N/A	MODEL TYPE:
					DWN		DATE		VIEW:	2.40mm Crimp Style Connectors
					CHKD		DATE		UNIT: mm/in	X9357HM-2x04B-N0
					APPD		DATE		SIZE: A4	DWG NO.:
										X-X9357HM-2x04B-N0
										WEIGHT
										1.0g
										SHEET
										1/1
										REVISION
										A0

REVISIONS

www.helloxkb.com

UNSPECIFIED TOLERANCES

XKB INDUSTRIAL PRECISION CO.,LIMITED

ΔX				XKB	ANGLAR	±5°
ΔX					L≤4	±0.2
ΔX					4<L≤16	±0.3
ΔX					16<L≤63	±0.4
MARK					L>63	±0.5