

HSF



RoHS

SPECIFICATION

Current Rating: 3 Amp
Insulation Resistance: 1000M ohms min
Contact Resistance: 20M ohms max
Dielectric Withstanding: AC500V
Operating Temperature: -65° C to +125° C
Contact Material: Brass
Insulator Material: PA9T, UL 94V-0 Black

Ordering Code:

PHIR01 - X - X - D - A-B-D - X - X - X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

① Series No:

② No. of Contacts
02 To 80

③ Contact Plating:

G0:Gold flash S0:Selective
G1:3U" Gold S1:Selective 3u"
G2:5u" Gold S2:Selective 5u"
G3:10u" Gold S3:Selective 10u"
G4:15u" Gold S4:Selective 15u"
G5:30u" Gold S5:Selective 30u"
SN:Tin





④ Connector Type
D: Dual

⑤ Pin Length:

A:0600=6.00mm

B:0600=6.00mm

D:0085=0.85mm

Please mark the desired
length in the A/B/D⑥ Insulator Material
E: PA9T⑦ Packing
A: Tray B: Bag
T: Tube⑧ Plastic High
H: 2.30mmRECOMMENDED P.C.B LAYOUT
(TOLERANCE ±0.05)


Unless Otherwise specified tolerance

X. XX: ±0.35

X. XX: ±0.20

X. X: ±0.25

X. XXX: ±0.15

SCALE:
As ShownUNIT:
mmDRAW
ZLADATE
11/27/2023CHECK
BobYangDATE
11/27/2023

3rd ANGLE PROJECTION

ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail:sales@antenk.com

TITLE:

2.2X3.0X2.3mm Pin Header Dual Row Right Angle Type

DRAWING NO: PHIR01-12-G0-D-0600-0080-0600-E-B-H1

PRODUCT NO: PHIR01-12-G0-D-0600-0080-0600-E-B-H1

REV

DESCRIPTION

DATE

1 2 3 4 5 6 7 8