


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.07.20	阿 树

- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:5A AC/DC
 - Withstanding Voltage:1000V AC/minute
 - Temperature range:-45°C+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤10mΩ

PART NO.:
X3025 W R-2x03 B-46 SN
① ② ③ ④ ⑤ ⑥ ⑦

①Series No
②Category:W-Wafer
③Welding Board Angle:R-Straight 90°
④Row No-Pin No: 2xXX-2x01P~2x12P
⑤Special NO:B-Without positing column
⑥Material:46-PA46 UL94V-0
66-PA66 UL94V-0
LP-LCP UL94V-0
⑦Planting:SN-Bright tin plating



Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2x01		6.65	2x07	18.00	24.65
2x02	3.00	9.65	2x08	21.00	27.65
2x03	6.00	12.65	2x09	24.00	30.65
2x04	9.00	15.65	2x10	27.00	33.65
2x05	12.00	18.65	2x11	30.00	36.65
2x06	15.00	21.65	2x12	33.00	39.65

X3025WR-2x03B-LPSN	LCP UL 94V-0	Brass	Tin-Plated	X3025H
X3025WR-2x03B-46SN	Nylon 46 UL 94V-0			
X3025WR-2x03B-66SN	Nylon 66 UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿 树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE:	3.00 mm Crimp Style Connectors
PART NO.:	X3025WR-2x03B-46SN
DWG NO.:	

SCALE	PAGE	REVISION
N/A	1/1	A1

XKB INDUSTRIAL PRECISION CO.,LIMITED