









## TYPE 2



Y型端子





14P-64P 双槽





6P 小鼻/无槽

TYPE C




6P 大鼻/无槽

TYPE A





8P 大鼻/无槽

TYPE A





6P 小鼻/单槽

TYPE B



8P 小鼻/单槽

TYPE B



10P-12P 单槽

Blank

### Specifications:

#### 规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ MAX

接触电阻: ≤20mΩ MAX

X9555 H3 -2x10- PT 01

① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:H3-HSG with TYPE 2

3.Row No-Pin No:2xXX-2x03P~2x32P

4.Special:NO:X Type A or Type B and Type C

Blank-conventional product

6.Material:PT-PBT UL94V-0

7.Plating:V01-Gold Flash

|                    |          |               |             |                    |                         |                  |
|--------------------|----------|---------------|-------------|--------------------|-------------------------|------------------|
| X9555H3-2x10-PTV01 | PBT      | BRASS         | Gold Flash  | X9555WV-2xXX       | XPD1.27-A28PXX-IDC      | X9555HI-2xXXA    |
|                    |          |               |             | X9555WR-2xXX       |                         | X9555HI-2xXXB    |
|                    |          |               |             | X9555WVS-2xXX      |                         | X9555HI-2xXXC    |
|                    |          |               |             | X9555WV-2xXX       |                         | X9555HI-2xXXA    |
| X9555H3-2x10-PTV01 | PBT      | BRASS         | Gold Flash  | X9555WR-2xXX       | XPD1.27-A28PXX-IDC      | X9555HI-2xXXB    |
|                    |          |               |             | X9555WVS-2xXX      |                         | X9555HI-2xXXC    |
|                    |          |               |             | X9555WV-2xXX       |                         | X9555HI-2xXXA    |
| PART NO            | Material | Material(pin) | Finish(pin) | Suitable XKB Wafer | Suitable XKB flat cable | Suitable XKB DIP |

| NUMBER OF POSITIONS | DIMENSION |       |           | NUMBER OF POSITIONS | DIMENSION |       |     |
|---------------------|-----------|-------|-----------|---------------------|-----------|-------|-----|
|                     | A         | B     | C         |                     | A         | B     | C   |
| 2x03                | 12.32     | 5.08  | 1.9       | 2x13                | 37.72     | 30.48 | 3.8 |
| 2x04                | 14.86     | 7.62  | 小1.9/大3.8 | 2x15                | 42.80     | 35.56 | 3.8 |
| 2x05                | 17.40     | 10.16 | 3.8       | 2x17                | 47.88     | 40.64 | 3.8 |
| 2x06                | 19.94     | 12.70 | 3.8       | 2x18                | 50.42     | 43.18 | 3.8 |
| 2x07                | 22.48     | 15.24 | 3.8       | 2x20                | 55.50     | 48.26 | 3.8 |
| 2x08                | 25.02     | 17.78 | 3.8       | 2x22                | 60.58     | 53.34 | 3.8 |
| 2x09                | 27.56     | 20.32 | 3.8       | 2x25                | 68.20     | 60.96 | 3.8 |
| 2x10                | 30.10     | 22.86 | 3.8       | 2x30                | 80.90     | 73.66 | 3.8 |
| 2x11                | 32.64     | 25.40 | 3.8       | 2x32                | 85.98     | 78.74 | 3.8 |
| 2x12                | 35.18     | 27.94 | 3.8       |                     |           |       |     |

|                                               |  |  |  |  |          |                        |
|-----------------------------------------------|--|--|--|--|----------|------------------------|
|                                               |  |  |  |  | ANGLAR   | ±5°                    |
| ΔX                                            |  |  |  |  | L≤ 4     | ±0.2                   |
| ΔX                                            |  |  |  |  | 4<L≤ 16  | ±0.3                   |
| ΔX                                            |  |  |  |  | 16<L≤ 63 | ±0.4                   |
| MARK                                          |  |  |  |  | L> 63    | ±0.5                   |
| DESCRIPTION                                   |  |  |  |  | DATE     | REVISED                |
| REVISIONS                                     |  |  |  |  | APPROVED | UNSPECIFIED TOLERANCES |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |  |  |  |  |          |                        |

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|      |  |             |                               |
|------|--|-------------|-------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE: 2.54mm IDC        |
| DWN  |  | VIEW:       | PART NO.: X9555H3-2x10-PTV01  |
| CHKD |  | UNIT: mm/in | DWG NO.: X-X9555H3-2x10-PTV01 |
| APPD |  | SIZE: A4    | WEIGHT                        |
|      |  |             | SHEET 1/1                     |
|      |  |             | REVISION A0                   |