







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面修正，升级整理图面	2024.9.27	阿树

电路原理图



PCB LAYOUT



NOTE:
Rating:DC 12V 50mA
Operating Force:200±100gf
Lifetime:10,000 Cycles

PAPT NO	L
SS-3456D-02-L1	2.0
SS-3456D-02-L2	3.0
SS-3456D-02-L3	4.0

			Terminal	
5	Terminal	10	Brass (030t)	Ag Plated
4	Contact spring	4	Phosphor branze	Ag Plated
3	Base	1	LCP	Black
2	Cover	1	SUS	Sliver
1	Keystake	1	PA46	Black
ITEM	PAPT NAME	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	SLIDE SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	SS-3456D-02-L2
APPROVED		SIZE:	A4	DWG NO.:	X-SS-3456D-02-L2

SCALE	PAGE	REVISION
N/A	1/1	A1