

Medical
electric
equipmentPower
Factor
Correction

World wide

Safety
Approvals

EMI

Inrush
current
limiting

OCP



OVP

Remote
ON/OFFParallel
Operation

1U

T-series



■ Features

Meets IEEE 802.3 and ANSI X3.263 standards .RoHS Compliant
 10/100/1000 Base-T, Surface Mount Type, Open Header
 Cable interface for isolation and low common mode emissions.
 Reflow soldering temperature: peak temperature $\leq 250^{\circ}\text{C}$ (10s)
 Reflow soldering frequency: It is recommended not to exceed 3 times
 Storage temperature range: -40°C to $+85^{\circ}\text{C}$
 Operating temperature range: 0°C to $+70^{\circ}\text{C}$


■ ROHS REACH marking

■ CE FCC marking

2 Specifications


Part No	OCL(uH min) @100KHz/0.1V	Turns Ratio(3%)		DCR (Ω) Max	Cww(Pri:Sec) pF Typ		Isolation Voltage(AC Vrms 1S)
TA24S02	350UH	1:1		0.9/1.2	35		1500V
Part No	Insertion loss (dB max) 1-100MHz	Return Loss(dB Min)MHz			CMRR(dB min)MHz		Crosstalk (dB min)MHz
		1-30	40~60	60~100	1-60	60~100	
TA24S02	-1.5	-18	-16	-12	-40	-30	-35

3 Mechanical




※unit: mm

4 Schematic



5 packing



※unit: mm

※ Packaging quantity : *pcs/roll *pcs/box

※ Outer box size: * L ** W ** H