



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2025.06.19	




- SPECIFICATIONS
- Voltage rating: 250V AC/DC
 - Current rating: 10A AC/DC
 - Withstanding Voltage: 1500V AC/minute
 - Temperature range: -40°C ~ +125°C
 - Insulation resistance: ≥ 1000MΩ
 - Contact resistance: ≤ 10mΩ
 - Material: Wafer PA66, UL94V-2
PIN Brass Tin-plated

PART NO.:

X5050 W V-03-N2 SN XX

Series No
Category: W-Wafer
Welding Board Angle: V-Stright 180°
Row No. Pin No: XX-03Pin
Material: N2-PA66 UL94V-2
Planting: SN-Bright Tin Plating
Color Blank-Natural Color



X5050WV-03-N2SN	Nylon 66 UL 94V-2	Brass	Tin-Plated	X5050H
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	VIEW:	MODEL TYPE: 5.08mm Crimp Style Connectors
CHECKED	UNIT: mm/in	PART NO.: X5050WV-03-N2SN
APPROVED	SIZE: A4	DWG NO.: X-X5050WV-03-N2SN