

1




2

3



4

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.18	阿树




P.C.B LAND DIMENSION



SPECIFICATION
1.Rating:DC 12V 50mA Max
2.Contact resistance: 100mΩ MAX
3.Insulation resistance: 100MΩ Min
4.Dielectric strength: 250VAC/min
5.Operating force: 180gf±50gf
6.Operating life: 100,000 cycles

PAPT NO	TS-1186D-B-B
Operating Force	B:160gf C:260gf
Height	H:4.5
Fixed column	A:With B:Without



CIRCUIT DIAGRAM

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	TACT SWITCH
APPROVED		SIZE: A4	PART NO.: TS-1186D-B-B
			DWG NO.: TS-1186D-B-B

1

2

3

4