

1.View and size(视图及尺寸)

Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	5000
2.Working Temperature (温度)	-55 ~+150 ℃
3.IP Rating (防护级别)	IP 50
4.Diameter of socket end(插套端直径)	φ0.5
5.Testing Voltage (测试电压)	600V
6.Working Voltage (工作电压)	500V
7.Rated Current (额定电流)	2.0A
8.Shell material(壳体材质)	Brass (chromium plating) shell and chuck nut/(nickel plating) pin sleeve and middleware/黄铜(镀镍)外壳和夹头螺母(镀镍)插销套和中间件
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)
10.Insulator material(绝缘体材质)	PPS


Sum up(总结)

Series(系列)	B
Shell style/model (外壳样式/型号)	TGG: Straight plug, cable collet and nut for fitting a bend relief 直基、电缆夹头和螺母, 用于安装弯曲凸起
Button (按键)	A button(一个按键)
Termination type (终止类型)	Male solder(公焊锡)
Line diameter awg(线材直径)	32~28AWG
Cable diameterφ (电缆直径)	φ4.3-5.2MM
Matching parts(配件)	ZGG.0B.P09.CLL

Location pin combination (定位销组合)

(编号) Number	Number of positioning pins(定 位销数量)	Angle(角 度)	Series(系列)-0B
G	One(1)	A	(Zero degrees)0°
A	Two(2)		Thirty degrees(30°)
B	Two(2)		Sixty degrees(60°)
C	Two(2)		Ninety degrees(90°)
D	Two(2)	β	135 degrees(135°)
E	Two(2)		145 degrees(145°)
F	Two(2)		155 degrees(155°)
J	Two(2)	γ	Forty-five degrees(45°)
K	Two(2)		Seventy degrees(70°)
L	Two(2)		80 degrees(80°)

	A	B	C√	ANGLE	
5-10	±0.02	±0.05	±0.1	0°~30°	±0.1°
50-100	±0.1	±0.15	±0.2	61°~90°	±0.5°
50-100	±0.15	±0.2	±0.25		
100~	±0.15%	±0.20%	±0.25%		



	A	L	M	S1	S2
MM	φ9.5	36	26	8.0	7
in	0.374	1.4173	1.0236	0.315	0.2756

