

Medical
electric
equipmentPower
Factor
CorrectionWorld
wideSafety
Approvals

EMI

Inrush
current
limiting

OCP



OVP

Remote
ON/OFFParallel
Operation

1U

H-series



■ Features

Meets IEEE 802.3 and ANSI X3.263 standards .RoHS Compliant

10/100Base-T, Surface Mount Type, Open Header

Cable interface for isolation and low common mode emissions.

Reflow soldering temperature: peak temperature $\leq 250^{\circ}\text{C}$ (10s)

Reflow soldering frequency: It is recommended not to exceed 3 times

Storage temperature range: -25°C to $+85^{\circ}\text{C}$

Operating temperature range: 0°C to $+70^{\circ}\text{C}$

■ ROHS REACH marking



■ CE FCC marking





2 Specifications

Part No	OCL(uH min) @100KHz/0. 1Vrms,8mA	Turns Ratio(3%)		DCR (Ω) Max	Cww(Pri:Sec) pF Typ		Isolation Voltage(AC Vrms 3S)
H1102NLT-TA	350UH	1:1		0.9/1.2	35		1500V
Part No	Insertion loss (dB max) 1~100MHz	Return Loss(dB Min) MHz			DMRR(dB min)MHz		Crosstalk(dB min)MHz
		1~30	40~60	60~100	1~60	60~100	1~100
H1102NLT-TA	-1.2	-18	-16	-14	-40	-30	-35

3 Mechanical




SUGGESTED PAD LAYOUT




※unit: mm

4 Schematic



5 packing



※unit: mm

※ Packaging quantity : 600pcs/roll 4800pcs/box

※ Outer box size: * L * * W * * H