










01 Pin




02~05 Pin






Guide Key : Inside Color : Natural



Guide Key : Left Side Color : Red



Guide Key : Right Side Color : Black



01 Pin

PART NO	DIM A	DIM B
01	/	/
02	17.22	7.92
03	25.14	15.84
04	33.06	23.76
05	40.98	31.68

Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Withstanding voltage:2500V AC/minute

耐受电压: 2500V AC/分钟

Temperature range:-40℃~+125℃

温度范围: -40℃~+125℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:5mΩ Max

接触电阻: 5mΩ Max

K 792100 W V - 04 S - N0 SN
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.K: XKBTEK-Car Connector

2.XKB Series No

3.Category:W-Wafer

4.Welding Board Angle:V-Stright 180°

5.Row No.Pin No:XX-01~05 Pin

6.Special No:S-With Positioning column

7.Material:N0-PA66+30%GF 94V-0

8.Plating:SN-Plated Tin or V01-Gole 1u"

9.Color:B-Black ;R-Red;Blank-Natural

Poles	10 AWG	12 AWG	14 AWG	16 AWG
1	30 A	25 A	20 A	15 A
2	25 A	20 A	18 A	15 A
3	25 A	20 A	18 A	15 A
4	22 A	18 A	15 A	13 A
5	22 A	18 A	15 A	13 A

PART NO	DIM A	DIM B
01	/	/
02	17.22	7.92
03	25.14	15.84
04	33.06	23.76
05	40.98	31.68

K792100WV-04S-N0SN	PA66	Phosphor Bronze	K792100WV
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 7.92mm Automobile connector
DWN	VIEW:	PART NO.: K792100WV-04S-N0SN
CHKD	UNIT: mm/in	DWG NO.: X-K792100WV-04S-N0SN
APPD	SIZE: A4	

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGULAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn