

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.11.08	阿树

SPECIFICATIONS:

- 1.VOLTAGE/CURRENT RATING: 30V/AC, DC.0.3A;
 - 2.WITHSTANDING VOLTAGE: 100V AC/ONE MINUTE;
 - 3.INSULATION RESISTANCE: 50MΩ MIN/100V DC.;
 - 4.CONTACT RESISTANCE: 90mΩ MAX./1mA,20mV AC,1KHz;
 - 5.DURABILITY: 30 CYCLES;
 - 6.OPERATING TEMPERATURE RANGE: -40°C TO 125°C
- MATERIAL:
- 1.INSULATOR: LCP UL 94V-0 BLACK;
 - 2.TERMINAL: PHOSPHOR BRONZE;
- PLATING:
- 1.TERMINAL: CONTACT AREA: GOLD 0.05 μm"MIN.
 - SMT LEAD: GOLD 0.025 μm" MIN.
 - UNDERPLATING: NICKEL 1 μm" MIN.

PART NO.:

X0408 F V S-80 A-LP V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ①Series No
- ②Category:F-Female
- ③Welding Board Angle:V-Straight 180°
- ④Welding Way: S-SMT
- ⑤Row No.Pin No:XX-10~100P
- ⑥Height:A=1.5
- ⑦Material:LP-LCP UL 94V-0 Black
- ⑧Plating:V01-Gold Flash;

HEIGHT		
H(Socket)	H(Plug)	Mating height
1.45	1.14	A=1.5

Poles	Dimensions(mm)			
	A	B	C	D
10	4.60	1.60	3.55	1.00
12	5.00	2.00	3.95	
20	6.60	3.60	5.55	
24	7.40	4.40	6.35	
30	8.60	5.60	7.55	1.50
34	9.40	6.40	8.35	2.30
40	10.60	7.60	9.55	3.20
50	12.60	9.60	11.55	
60	14.60	11.60	13.55	
70	16.60	13.60	15.55	
80	18.60	15.60	17.55	
90	20.60	17.60	19.55	
100	22.60	19.60	21.55	

X0408FVS-80A-LPV01	LCP	Phosphor Bronze	X0407W
PART NO	Material	Material(Pin)	Suitable XKB Wafer




DESIGN	阿树	VIEW:	MODEL TYPE: 0.4mm BTB Connector
CHECKED		UNIT: mm/in	PART NO.: X0408FVS-80A-LPV01
APPROVED		SIZE: A4	DWG NO.:

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/2	A1



Recommended PCB Layout

