




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.06.23	阿树
A2	ECN-P-2026051301	ⒶX4	产品尺寸变更	2026.05.13	山楂



- 1.Rating:DC30V 100mA
- 2.Contact Resistance:500m Ω Max
- 3.Insulation Resistance:>100MΩ DC500V
- 4.Withstand Voltage:AC500V 1min
- 5.Soldering Temper:235±5°C 5s
- 6.Electrical Life:100,000 cycles
- 7.Mechanical Life:300,000 cycles
- 8.Ambient Temper Used:-25°C~+85°C
- 9.Ambient Humidity Used:≤85%~+40°C
- 10.Operating Force:50gf max



7	Pressing handle	SUS	
6	Contact	Silver alloy	
5	Terminal	C2680	Ag Plated
4	Shrapnel	C5210	
3	Button	PBT	White
2	Upper cover	PBT	Black
1	Bottom cap	PBT	White
NO	NAMF	MATERIAL	PLATING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	山楂	VIEW:	MODEL TYPE: MICRO SWITCH
CHECKED		UNIT: mm/in	PART NO.: DM1-12UP-1
APPROVED		SIZE: A4	DWG NO.: