

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.21	阿树

Specifications:
规格:
Voltage rating:50V AC/DC
额定电压: 50V AC/DC
Current rating:0.5A AC/DC
额定电流: 0.5A AC/DC
Withstanding voltage:250V AC/minute
耐受电压: 250V AC/分钟
Temperature range:-40℃+105℃
温度范围: -40℃+105℃
Insulation resistance:500MΩ
绝缘电阻: 500MΩ
Contact resistance:100mΩ
接触电阻: 100mΩ

PART NO.:
X0815 W V S-80 C S-9T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-30-60Pin
⑥Category:C-19.75mm Height
⑦Special No:S-With positioning column
⑧Material:9T-PA9T UL94V-0
CAP Material:PA6T UL94V-0
⑨Plating:Gold Plated 3u" MIN

Poles	Dimensions(mm)					
	A	B	C	D	E	F
30	11.20	13.00	16.30	13.70	16.10	15.00
40	15.20	17.00	20.30	17.70	20.10	19.00
50	19.20	21.00	24.30	21.70	24.10	23.00
60	23.20	25.00	28.30	25.70	28.10	27.00

X0815WVS-80CS-9TV01	PA9T	Phosphor Bronze	X0815FVS-A	24.7mm±0.5
			X0815FVS-B	20.95mm±0.5
PART NO	Material	Material(Pin)	Suitable XKB Wafer	Mating Height

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 0.8mm BTB Connector
CHECKED		UNIT:	mm/in	PART NO.: X0815WVS-80CS-9TV01
APPROVED		SIZE:	A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A1