


Main technical indicators(主要技术指标)	
1.Mating (插拔次数)	5000
2.Working Temperature (温度)	-55--+150 ℃
3.IP Rating (防护级别)	IP 54
4.Diameter of socket end(插合端直径)	φ1.3
5.Testing Voltage (测试电压)	1750V
6.Working Voltage (工作电压)	1600V
7.Rated Current (额定电流)	14A
8.Shell material(壳体材质)	Brass (chromium plating) shell and chuck nut/(镀铬) 黄铜(镀镍) 外壳和夹头螺母/ (镀镍)插销套和中间件
9.Pin Material(插针材料)	Copper alloy gold plating(铜合金镀金)
10.Insulator material(绝缘体材质)	PPS

Sum up(总结)	
Series(系列)	B
Shell style/model (外壳样式/型号)	TEG: Straight plug, cable collet, front seal and nut for fitting a bend relief (IP 54 when mated) 直塞、电缆夹头、前密封件和用于安装弯曲补偿(配合时IP54)
Button (按键)	A button(一个按键)
Termination type (终止类型)	Male solder(公焊锡)
Line diameter awg(线材直径)	28-20AWG
Cable diameterφ (电缆直径)	φ8.3-9.2MM
Matching parts(配件)	ZGG.2B.P05.CLL


Location pin combination (定位销组合)				
(编号) Numder	Number of positioning pins/定位销数量	Angle(角度)	Series(系列)~2B	
G	One(1)		(Zero degrees)0°	
A	Two(2)	A	Thirty degrees(30°)	
B	Two(2)		Forty-five degrees(45°)	
C	Two(2)		Sixty degrees(60°)	
D	Two(2)	γ	95 degrees (95°)	
E	Two(2)	β	120 degrees(120°)	
F	Two(2)		145 degrees(145°)	
J	Two(2)	A	37.5degrees(37.5°)	
K	Two(2)		52.5degrees(52.5°)	
L	Two(2)	γ	Seventy degrees(70°)	
	A	B	C/√	ANGLE
5-10	±0.02	±0.05	±0.1	0°-30° ±0.1°
50-100	±0.1	±0.15	±0.2	61°-90° ±0.5°
50-100	±0.15	±0.2	±0.25	
100-	±0.15%	±0.20%	±0.25%	



	A	L	M	S1	S2
MM	φ16.5	48	36	13.0	12
in	0.6496	1.8898	1.4173	0.512	0.4725



Welded surface
(焊接面)



Positive view
(正视图)



Solder core
(焊接型公胶芯)

TE G. 2B. P05.C L A D 92 H

- Model(型号)
- Positioning pin(定位销)
- Series(系列)
- Needle core configuration(针芯配置)
- Outer casing(外壳)
- Insulator(绝缘体)
- Needle core(针芯)
- Type of clamp(线夹类型)
- Cable diameter(电缆直径)
- SH means a sheath type, not a cover type.
(H表示护套型，不表示为不带护套型))

DESIGNED (设计)	DATE (日期)	SCALE (比例)	N/A (不适用)	MODEL TYPE 型号类型: TEG.2B.P05 CLAD 92H
CHECKED (校对)	DATE (日期)	VIEW (视图)		PART NO. 2B5-core plug 名称: 2B5芯插头
APPROVED (审核)	DATE (日期)	UNIT (单位)	MM	DWG NO.:
REVISIONS		MATERIAL (材料)		
www.helloxkb.com www.helloxkb.cn		XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT (重量)
				SHEET (张)
				1/1
				REVISION (修订)
				A0