

HSF



RoHS





SPECIFICATION

Current Rating: 1.5 Amp
Insulation Resistance: 1000M ohms min
Contact Resistance: 20M ohms max
Dielectric Withstanding: AC500V
Operating Temperature: -65°C to +125°C
Contact Material: Brass
Insulator Material: PA6T,UL 94V-0 Black

Ordering Code:

PHDR04 - X - X - D - A-D-B - X - X - X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No:
② No. of Contacts
02 To 80
③ Contact Plating:
G0: Gold flash S0: Selective
G1: 3u" Gold S1: Selective 3u"
G2: 5u" Gold S2: Selective 5u"
G3: 10u" Gold S3: Selective 10u"
G4: 15u" Gold S4: Selective 15u"
G5: 30u" Gold S5: Selective 30u"
SN: Tin
④ Connector Type
D: Dual
⑤ Pin Length:
A: 0400=4.00mm
D: 0075=0.75mm
B: 0280=2.80mm
Please mark the desired length in the A/D/B
- ⑥ Insulator Material
A: PBT
B: PA6T
C: LCP
D: PA46
E: PA9T
⑦ Packing:
A: Tray
B: Bag
T: Tube
U: Tube+CAP
R: Tape&Reel
W: Tape&Reel+CAP
⑧ Plastic High
H1: 1.5mm
H2: 2.0mm



PCB LAYOUT

Standard IE P/N :

PHDR04-32G0D040000750280BBH2

A	D	B
4.0	0.75	2.8

Unless Otherwise specified tolerance
X. ± 0.35 X.XX: ± 0.20
X.X: ± 0.25 X.XXX: ± 0.15

Optional

SCALE:

As Shown

UNIT:

mm

DRAW

YG ZHONG

DATE


03/22/2016

CHECK

BobYang

DATE

03/22/2016



3rd ANGLE PROJECTION



ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail:sales@antenk.com

TITLE:

2.00mm Pin Header Dual Row Angle Type

DRAWING NO:

PHDR04-32G0D040000750280BBH2

PRODUCT NO:

PHDR04-32G0D040000750280BBH2

REV

Increase packing method and material

2016/10/25

DESCRIPTION

DATE