



Recommended PCB Layout
General Tolerance±0.05

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/ 分钟

Temperature range:-25 ℃ -+85℃

温度范围: -25℃ -+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤30mΩ

接触电阻: ≤30mΩ

After environmental testing:≤50mΩ

环境测试后: ≤50兆欧

X2026 W V -2x08D-46SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:V-Straight 180°

4.Welding Way:Blank-DIP

5.Row No-Pin No:2xXX-2x02P~2x22P

6.Plug the Pin&Special NO:

D-With Lock in the middle

7.Material:46-PA46 94V-0.9T-PA9T 94V-0

4T-PA4T 94V-0

8.Plating Category:SN-Bright Tin Plating

V03-All Gold-Plated 3u"

9.Color:Blank-Natural Color

poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	6.00	4.90	2x10	18.00	22.00	20.90	2x18	34.00	38.00	36.90
2x03	4.00	8.00	6.90	2x11	20.00	24.00	22.90	2x19	36.00	40.00	38.90
2x04	6.00	10.00	8.90	2x12	22.00	26.00	24.90	2x20	38.00	42.00	40.90
2x05	8.00	12.00	10.90	2x13	24.00	28.00	26.90	2x30	58.00	62.00	60.90
2x06	10.00	14.00	12.90	2x14	26.00	30.00	28.90				
2x07	12.00	16.00	14.90	2x15	28.00	32.00	30.90				
2x08	14.00	18.00	16.90	2x16	30.00	34.00	32.90				
2x09	16.00	20.00	18.90	2x17	32.00	36.00	34.90				

X2026WV-2x08D-4T SN	PA4T 94V-0	Brass	Tin-Plated	X2026H-D
X2026WV-2x08D-9T V03	PA9T 94V-0		Gold-Plated 3u"	
X2026WV-2x08D-46 SN	PA46 94V-0		Tin-Plated	
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Housing

Wire to board connector

DSND		DATE		SCALE: N/A	MODEL TYPE:
DWN		DATE		VIEW:	2.00mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	PART NO.: X2026WV-2x08D-46SN
APPD		DATE		SIZE: A4	DWG NO.: X-X2026WV-2x08D-46SN
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0

					units: mm
Δ X					tolerance:
Δ X					X.X ±0.2mm
Δ X					X.XX ±0.1mm
MARK					X.XXX ±0.05mm
REVISIONS					UNSPECIFIED TOLERANCES
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					