




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.09.12	阿树
/	/		/	/	/



■SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding Voltage:800V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ



PCB LAYOUT

PART NO.:

X2026 W V-2x07 D-46 V01
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:V-Stright 180°
- ④Row No.Pin No:2xXX-2x02~2x18Pin
- ⑤Special No:D-With Lock
- ⑥Material:46-PA46 UL94V-0
- ⑦Plating Category:V01-ALL Gold-Plated 1U"
V03-ALL Gold-Plated 3U"

poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B
2x02	2.00	6.00	2x11	20.00	24.00
2x03	4.00	8.00	2x12	22.00	26.00
2x04	6.00	10.00	2x13	24.00	28.00
2x05	8.00	12.00	2x14	26.00	30.00
2x06	10.00	14.00	2x15	28.00	32.00
2x07	12.00	16.00	2x16	30.00	34.00
2x08	14.00	18.00	2x17	32.00	36.00
2x09	16.00	20.00	2x18	34.00	38.00
2x10	18.00	22.00			

X2026WV-2x07D-46V01	PA46 94V-0	Brass	Gold-Plated 1u"	X2026H-D
X2026WV-2xXXD-46V03			Gold-Plated 3u"	
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEWS	UNIT: mm/in	MODEL TYPE: 2.00mm Crimp Style Connector
CHECKED		UNIT: mm/in		PART NO.: X2026WV-2x07D-46V01
APPROVED		SIZE: A4		DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0