



PCB LAYOUT

Specifications:

规格:

Voltage rating:125V AC/DC

额定电压: 125V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X9555 W V S - 2x08 - 9T V01

① ② ③ ④ ⑤ ⑥ ⑦

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Stright 180°

4.Welding Way:S-SMT

5.Row No.Pin No:2xXX-2x03~2x32P

6.Material:9T-PA9T UL94V-0

7.Plating:V01-Gold Flash

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2x03	15.24	5.08	12.94	2x14	43.18	33.02	40.88
2x04	17.78	7.62	15.48	2x15	45.72	35.56	43.42
2x05	20.32	10.16	18.02	2x16	48.26	38.10	45.96
2x06	22.86	12.70	20.56	2x17	50.80	40.64	48.50
2x07	25.40	15.24	23.10	2x18	53.34	43.18	51.04
2x08	27.94	17.78	25.64	2x20	58.42	48.26	56.12
2x09	30.48	20.32	28.18	2x22	63.50	53.34	61.12
2x10	33.02	22.86	30.72	2x25	71.12	60.96	68.82
2x11	35.56	25.40	33.26	2x30	83.82	73.66	81.82
2x12	38.10	27.94	35.80	2x32	88.90	78.74	86.60
2x13	40.64	30.48	38.34	/			

X9555WVS-2x08-9TV01	PA9T	Brass	X9555H
PART NO	Material	Material(Pin)	Suitable XKB Housing

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5

REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connector
DWN		VIEW:	
CHKD		UNIT: mm/in	PART NO.: X9555WVS-2x08-9TV01
APPD		SIZE: A4	DWG NO.: X-X9555WVS-2x08-9TV01
		WEIGHT	SHEET
			REVISION
		1/1	A0