




2 CKT




3 CKT




4 CKT




5 CKT






6 CKT



7 CKT



8 CKT



Specifications:

规格:

Voltage rating:400V AC/DC

额定电压: 400V AC/DC

Current rating:14A AC/DC

额定电流: 14A AC/DC

Withstanding voltage:1800V AC/minute

耐受电压: 1800V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:15mΩ Max

接触电阻: 15mΩ Max

X3501 HL - 03 - N0 BK

① ② ③ ④ ⑤ ⑥

1.Series No

2.Category:HL-Matching rubber shell
row line lock

3.Row No.Pin No:XX-02~08P

4.Material:N0-Nylon66 UL94V-0

5.Color:BK-Black ; N-Natural

Poles	Dimensions(mm)	
	A	B
02	3.50	8.20
03	7.00	11.70
04	10.50	15.20
05	14.00	18.70
06	17.50	22.20
07	21.00	25.70
08	24.50	29.20

X3501HL-03-N0BK	Black	Nylon66	X3501H
X3501HL-03-N0N	Natural		
PART N0	Material	Material	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 3.5mm Crimp Style Connector
DWN		VIEW:	
CHKD		UNIT: mm/in	PART NO.: X3501HL-03-N0BK
APPD		SIZE: A4	DWG NO.: X-X3501HL-03-N0BK

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
DESCRIPTION		DATE	REVISED	APPROVED		