





Code-X	H
A	3.8
B	4.3
C	4.5
D	5.0
E	5.5
F	6.0
G	6.5
H	7.0
I	7.5
J	8.0
K	8.5
L	9.0



PCB.Circuit poribbited area

PAPT NO	TC-1109DE-C-I
Operating Force	A:100gf B:160gf C:260gf
Height	Code-x

- 1.Rated current: Voltage:DC 12V 50mA
- 2.Contact resistance: $\leq 100\text{ m}\Omega$
- 3.Insulation resistance: $\geq 100\text{ M}\Omega$
- 4.The intensity of operations: $250 \pm 50\text{gf}$
- 5.Life requirements: 50000 times
- 6.Withstand voltage: AC250V 1 minute
- 7.All materials comply with RoHS standards
- 8.Operating temperature range: $-20^{\circ}\text{C} \sim +70^{\circ}\text{C}$
- 9.Travel to closure: $0.20 \pm 0.10\text{mm}$

⑤	Terminal	Brass	2	Ag Plating
④	Shrapnel	Sus	1	Ag Plating
③	Housing	PPA	1	Black
②	Cover	Brass	1	Ni Plating
①	Button	PPA	1	Black
ITEM	PART NAME	MATERIAL	QTY	FINISHING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	

XKIB 星城 Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: TACT SWITCH		
CHECKED		UNIT: mm/in	PART NO.: TC-1109DE-C-I		
APPROVED		SIZE: A4	DWG NO.: TC-1109DE-C-I		
PRECISION CO., LIMITED			SCALE N/A	PAGE 1/1	REVISION A1