





Technical drawing of a 12-pin connector. The drawing shows a top view of the connector with 12 pins arranged in two rows of six. The overall width is dimensioned as $8.64 [0.340]$. The overall height is dimensioned as $4.20 [0.165]$. The distance between the center of the first pin and the center of the last pin in a row is dimensioned as $A \pm 0.20$. The distance from the left edge of the connector to the center of the first pin is dimensioned as $4.20 [0.165]$. The drawing includes a circular feature on the left side, labeled with a circled '12', and a circular feature on the right side, labeled with a circled '12'.



环境测试后: ≤ 20 兆欧

01 02 03 04 05 06 07 08 09

09 Color:Blank-natural color

Poles	Dimensions(mm)	
	A	B
2*07	25.20	40.00
2*08	33.60	48.40
2*09	46.20	61.00

X9357WV-2x09B-N0SN	Nylon 66 UL 94V-0	Phorphos Bronza	Tin-Plated	X9357HM-B
X9357WV-2x09B-N2SN	Nylon 66 UL 94V-2	Phorphos Bronza	Tin-Plated	X9357HM-B
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

XKB							DSND		DATE		SCALE: N/A	MODEL TYPE: 4.20 mm Crimp Style Connectors		
Δx				XKB	ANGULAR	±5°	DWN		DATE		VIEW: 	PART NO.: X9357WV-2x09B-N0SN		
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9357WV-2x09B-N0SN		
Δx					4<L ≤ 16	±0.3								
Δx					16<L ≤ 63	±0.4	APPD		DATE		SIZE: A4	X-X9357WV-2x09B-N0SN		
MARK	DESCRIPTION			DATE	REVISED	APPROVED							L > 63	±0.5
REVISIONS							XKB INDUSTRIAL PRECISION CO.,LIMITED							
UNSPECIFIED TOLERANCES														
www.helloxkb.com							WEIGHT 1.0g						SHEET 1/1	REVISION A0