

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.06.13	阿树
/	N/A		/	/	/

PART NO.:

X2026 W V S-2x04 D1-LP SW XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

Specifications
Current rating:3A AC,DC
Voltage rating:250V AC,DC
Temperature range:-40°to+105°
Contact resistance:10mΩ Max
Insulation resistance:1000MΩ Min
Withstanding voltage:800V AC/minute
Pin Material:Foggy Tin Material: LCP

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way: S-SMT
⑤Row No.Pin No:2xXX-2x02~2x20Pin
⑥Plug the Pin&Special N0:
D1-With Lock in the middle
⑦Material:LCP-LCP UL94V-0;
46-PA46 UL94V-0;
⑧Planting: SW-Matte Tin;SN-Bright Tin Plated
⑨Color:Blank-Natural Color
B-Black;W-White

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2x02	2.00	6.00	3.00	2x13	24.00	28.00	21.00
2x03	4.00	8.00	3.00	2x14	26.00	30.00	23.00
2x04	6.00	10.00	3.00	2x15	28.00	32.00	25.00
2x05	8.00	12.00	5.00	2x16	30.00	34.00	27.00
2x06	10.00	14.00	7.00	2x17	32.00	36.00	29.00
2x07	12.00	16.00	9.00	2x18	34.00	38.00	31.00
2x08	14.00	18.00	11.00	2x19	36.00	40.00	33.00
2x09	16.00	20.00	13.00	2x20	38.00	42.00	35.00
2x10	18.00	22.00	15.00	2x21	40.00	44.00	37.00
2x11	20.00	24.00	17.00	2x22	42.00	46.00	39.00
2x12	22.00	26.00	19.00				

X2026WVS-2x04D1-LPSWB	LCP UL94V-0	BRASS	Matte Tin	X2026H-DB
X2026WVS-2x04D1-46SNW	PA46 UL94V-0		TIN-PLATED	
PART NO.	MATERIAL	MATERIAL(PIN)	FINISH(PIN)	Suitable XKB

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: Terminal 2.00mm Crimp Style Connector
CHECKED		UNIT:	mm/in	PART NO.: X2026WVS-2x04D1-LPSWB
APPROVED		SIZE:	A4	DWG NO.: X-X2026WVS-2x04D1-LPSWB

SCALE	PAGE	REVISION
N/A	1/1	A0