

1

2



3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.10	阿树

A

A



■SPECIFICATIONS



- Voltage rating:250V AC/DC
- Current rating:2A AC/DC
- Withstanding Voltage:1000V AC/minute
- Temperature range:−40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ

PART NO.:

X2016 W R-02 B R-LP SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

B



B



- ①Series No
②Category:W—Wafer
③Welding Board Angle:R—Stright 90°
④Row No.Pin No:XX—02~16Pin
⑤Special No:B—With Baffle
⑥Special No:R—DIP 2.2mm
⑦Material: LP—LCP 94V-0,Natural
⑧Planting:SN—Tin Plating

C

C



Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	2.00	4.90	6.00	10	18.00	20.90	22.00
03	4.00	6.90	8.00	11	20.00	22.90	24.00
04	6.00	8.90	10.00	12	22.00	24.90	26.00
05	8.00	10.90	12.00	13	24.00	26.90	28.00
06	10.00	12.90	14.00	14	26.00	28.90	30.00
07	12.00	14.90	16.00	15	28.00	30.90	32.00
08	14.00	16.90	18.00	16	30.00	32.90	34.00
09	16.00	18.90	20.00				

D

D

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.00mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X2016WR-02BR-LPSN
APPROVED		SIZE:	A4	DWG NO.:	X-X2016WR-02BR-LPSN

X2016WR-02BR-LPSN	LCP	Brass	X2016H
PART NO	Material	Material(Pin)	Suitable XKB Housing

1

2

3

4